

Engineering Specification

Job Name _____
Orion Representative _____
Quantity Required _____

Contractor Signature _____
Approval Date _____
Contractor's P.O. No. _____

Whiteline PVDF
Ball Valves
Socket Fusion Ball Valves
PVDF Schedule 80

Specification

Orion Whiteline PVDF Ball Valves will be manufactured from virgin unpigmented PVDF (polyvinylidene fluoride) to be fully compatible with the Orion high purity Whiteline system. All valves will test to 150 psi @73°F (23°C). Each ball valve will be individually bagged.

Call customer service if you need assistance with technical details.

True Union Ball Valve - BV

Qty.	Part No.	Size (in.)	A	H	H1	L	D	Weight (oz.)	
								PP	PVDF
	950357	1/2	3.1	1.9	1.0	4.2	2.0	5.49	10.56
	950358	3/4	3.8	2.6	1.2	4.8	2.5	8.19	15.52
	950359	1	3.8	2.6	1.4	5.5	2.8	10.66	20.48
	950360	1 1/2	4.5	3.5	2.2	6.8	4.1	24.42	50.40
	950361	2	4.5	3.5	2.2	7.9	4.1	36.48	75.52


Threaded Ball Valve End (2 Qty. Req/BV)		
	751514	1/2
	751529	3/4
	751512	1
	751510	1 1/2
	751513	2

Note: Larger sizes may be available. Contact Oriontechs@wattswater.com.
All dimensions are +/- 0.25".
All weights are approximate.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Orion product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Orion Technical Service. Orion reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Orion products previously or subsequently sold.



A WATTS Brand

USA: T: (800) 334-6259 • OrionFittings.com
Canada: T: (888) 208-8927 • OrionFittings.ca
Latin America: T: (52) 55-4122-0138 • OrionFittings.com