

Foodservice Specification Guide

Blue Hose® Gas Connector Kits
& Accessories



100% Leak
Tested

Over 185 Million
Safe Installations

Dormont.com

Dormont®
A **WATTS** Brand

Dormont Blue Hose® Moveable Gas Connector Kit with Excess Flow Valve

1675KIT48EFV

3/4 inch inside diameter by 48 inch long hose to have stress guard rotation end fittings, stainless-steel braid, and blue PVC antimicrobial coating. Kit includes industry exclusive Excess Flow Valve, exclusive SnapFast® Push-to-Connect Quick Disconnect, 1 full port valve, 2 elbows, and 1 coiled restraining cable with hardware. *Lifetime Limited Warranty.*

- Revolutionary Excess Flow Valve technology provides protection from gas leaks caused by a disconnected or ruptured gas connector.
- Each gas connector is 100% leak tested to meet and exceed applicable codes and standards—providing a high quality, safe connection for the customer.
- SnapFast Push-to-Connect makes connecting and disconnecting moveable equipment safe and easy for cleaning, maintenance, and service.
- SnapFast industry exclusive only available with the Dormont Blue Hose.



Dormont Blue Hose® Moveable Gas Connector Kit with Excess Flow Valve

1675KITS48EFV

3/4 inch inside diameter by 48 inch long hose to have stress guard rotation end fittings, stainless-steel braid, and blue PVC antimicrobial coating. Kit includes industry exclusive Excess Flow Valve, exclusive SnapFast® Push-to-Connect Quick Disconnect, 1 Swivel Max® 360 multi-plane rotational device, 1 full port valve, 1 elbow, and 1 coiled restraining cable with hardware. *Lifetime Limited Warranty.*

- Revolutionary Excess Flow Valve technology provides protection from gas leaks caused by a disconnected or ruptured gas connector.
- Each gas connector is 100% leak tested to meet and exceed applicable codes and standards—providing a high quality, safe connection for the customer.
- SnapFast Push-to-Connect makes connecting and disconnecting moveable equipment safe and easy for cleaning, maintenance, and service.
- SnapFast industry exclusive is only available with the Dormont Blue Hose.
- Swivel MAX prevents transmission of strain to connector and expands aisle space by allowing equipment to be moved closer to the wall.



Dormont Blue Hose® Moveable Gas Connector Kit with Excess Flow Valve

1675KIT2S48EFV

3/4 inch inside diameter by 48 inch long hose to have stress guard rotation end fittings, stainless-steel braid, and blue PVC antimicrobial coating. Kit includes industry exclusive Excess Flow Valve, exclusive SnapFast® Push-to-Connect Quick Disconnect, 2 Swivel Max® 360 multi-plane rotational device, 1 full port valve, and 1 coiled restraining cable with hardware. *Lifetime Limited Warranty.*

- Revolutionary Excess Flow Valve technology provides protection from gas leaks caused by a disconnected or ruptured gas connector.
- Each gas connector is 100% leak tested to meet and exceed applicable codes and standards—providing a high quality, safe connection for the customer.
- SnapFast Push-to-Connect makes connecting and disconnecting moveable equipment safe and easy for cleaning, maintenance, and service.
- SnapFast industry exclusive is only available with the Dormont Blue Hose.
- Swivel MAX prevents transmission of strain to connector and expands aisle space by allowing equipment to be moved closer to the wall.



Dormont Blue Hose® Moveable Gas Connector Kit

1675KIT48

3/4 inch inside diameter by 48 inch long hose to have stress guard rotation end fittings, stainless-steel braid, and blue PVC antimicrobial coating. Kit includes industry exclusive SnapFast® Push-to-Connect Quick Disconnect, 1 full port valve, 2 elbows, and 1 coiled restraining cable with hardware. *Lifetime Limited Warranty.*

- Each gas connector is 100% leak tested to meet and exceed applicable codes and standards—providing a high quality, safe connection for the customer.
- SnapFast Push-to-Connect makes connecting and disconnecting moveable equipment safe and easy for cleaning, maintenance, and service.
- SnapFast industry exclusive only available with the Dormont Blue Hose.



Dormont Blue Hose® Moveable Gas Connector Kit

1675KITS48

3/4 inch inside diameter by 48 inch long hose to have stress guard rotation end fittings, stainless-steel braid, and blue PVC antimicrobial coating. Kit includes industry exclusive SnapFast® Push-to-Connect Quick Disconnect, 1 Swivel Max® 360 multi-plane rotational device, 1 full port valve, 1 elbow, and 1 coiled restraining cable with hardware. *Lifetime Limited Warranty.*

- Each gas connector is 100% leak tested to meet and exceed applicable codes and standards—providing a high quality, safe connection for the customer.
- SnapFast Push-to-Connect makes connecting and disconnecting moveable equipment safe and easy for cleaning, maintenance, and service.
- SnapFast industry exclusive is only available with the Dormont Blue Hose.
- Swivel MAX prevents transmission of strain to connector and expands aisle space by allowing equipment to be moved closer to the wall.



Dormont Blue Hose® Moveable Gas Connector Kit

1675KIT2S48

3/4 inch inside diameter by 48 inch long hose to have stress guard rotation end fittings, stainless-steel braid, and blue PVC antimicrobial coating. Kit includes industry exclusive SnapFast® Push-to-Connect Quick Disconnect, 2 Swivel Max® 360 multi-plane rotational device, 1 full port valve, and 1 coiled restraining cable with hardware. *Lifetime Limited Warranty.*

- Each gas connector is 100% leak tested to meet and exceed applicable codes and standards—providing a high quality, safe connection for the customer.
- SnapFast Push-to-Connect makes connecting and disconnecting moveable equipment safe and easy for cleaning, maintenance, and service.
- SnapFast industry exclusive is only available with the Dormont Blue Hose.
- Swivel MAX prevents transmission of strain to connector and expands aisle space by allowing equipment to be moved closer to the wall.



Dormont Blue Hose® Moveable Gas Connector Kit

16100KIT48

1 inch inside diameter by 48 inch long hose to have stress guard rotation end fittings, stainless-steel braid and blue PVC antimicrobial coating. Kit includes industry exclusive SnapFast® Push-to-Connect Quick Disconnect, 1 full port valve, 2 elbows, and 1 coiled restraining cable with hardware. *Lifetime Limited Warranty.*

- Each gas connector is 100% leak tested to meet and exceed applicable codes and standards—providing a high quality, safe connection for the customer.
- SnapFast Push-to-Connect makes connecting and disconnecting moveable equipment safe and easy for cleaning, maintenance, and service.
- SnapFast industry exclusive is only available with the Dormont Blue Hose.



Dormont Blue Hose® Moveable Gas Connector Kit

1675KITCF48

3/4 inch inside diameter by 48 inch long hose to have stress guard rotation end fittings, stainless-steel braid, and blue PVC antimicrobial coating. Kit includes Safety Quik® Combination Push-to-Connect Quick Disconnect and gas valve in one that prevents gas connector from being disconnected until gas valve is shut off, 2 elbows, and 1 coiled restraining cable with hardware. *Lifetime Limited Warranty.*

- Each gas connector is 100% leak tested to meet and exceed applicable codes and standards—providing a high quality, safe connection for the customer.
- Safety Quik will not allow gas valve to be opened until the connector is re-connected.



Dormont Safety-Set® Positioning System With Antimicrobial Additive

PS

Designed to return caster-mounted equipment to a specific spot beneath fire suppression or ventilation systems after every cleaning. Accommodates 3", 4", 5", and 6" casters and withstands up to 1,000 lbs. of crush force. Meets NFPA Codes 17A and 96; Can be used with all caster-mounted equipment. Includes 2 Safety-Set units with thumb screw and hardware pack.

- Safety-Set helps ensure that gas equipment is situated beneath fire suppression or ventilation systems.
- Open-floor design allows equipment to rest level on the floor to help ensure even cooking.



Dormont Swirl Hose Water Supply Line Kit

71-1115-48

1/4 inch inside diameter by 48 inch long hose to be Lead Free*, durable, retractable NSF-Certified Polyurethane. Includes 2-way stainless-steel Quick Disconnect that allows equipment moving for cleaning without disconnecting water supply. Includes male adapter/female elbow. Maximum temperature rating of 160 degrees F with maximum operating pressure of 100 PSIG.

- Flexible design easily extends and retracts without damage versus a Copper Swirl Hose.
- Perfect application with ice machines and beverage equipment.




Dormont Combi-Oven Water Connector

CMB37BP2Q48

3/8 inch inside diameter by 48 inch long hose to be Lead Free*, stainless-steel corrugated braid, coated in gray antimicrobial PVC. Includes Lead Free* water Quick Disconnect 2-way coupling that shuts off water at equipment and supply. NSF Listed to NSF/ANSI 169 and NSF/ANSI 372. Maximum temperature rating of 225 degrees F with maximum operating pressure of 150 PSI.

- Each connector is 100% leak tested to meet and exceed applicable codes and standards—providing a high quality, safe connection for the customer.




* The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

[illegible]

[illegible]

[illegible]



The Dormont Difference

For 70+ years, the Food Service Industry has trusted Dormont. Get the same quality, flexibility, and safety trusted in commercial kitchens across the globe at Dormont, your one-stop shop for safe gas, water, and steam connectors.

- We Make What We Sell
- We Leak Test Every Gas Connector 100%
- We Meet or Exceed All Agency Standards
- We Use Only 304 Stainless Steel - Guaranteed
- Assembled in America with Foreign Sourced Components
- We Invented the Commercial Gas Hose
- Only ISO 9001-2015 Registered Manufacturer of Gas Connectors. 1993
- Manufactured More Than 185,000,000 Gas Connectors in Our 70+ Year History

Scan for Full Dormont
Foodservice Catalog



USA: T: (800) 367-6668 • F: (724) 733-4808 • Dormont.com
Canada: T: (888) 208-8927 • F: (905) 481-2316 • Dormont.ca
Latin America: T: (52) 55-4122-0138 • Dormont.com