Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

CLX-Ex

Online Residual Chlorine Monitor for Hazardous Environments

The HF scientific CLX-Ex Online TRO and Chlorine Monitor is a rugged, safe, and low maintenance instrument for shipboard ballast water treatment systems that require continuous monitoring and control of Total Residual Oxidant (TRO) levels in hazardous environments. User selectable cycle times, 4-20mA and RS-485 with Modbus output that can be used to control feed pumps and a user selectable alarm allows complete manual or automatic control of chlorine dosing.

Features

- Optimized for marine applications
- For use in explosive atmospheres where combustible fuel vapors may be present

Housing certified for Class 1, Division 1, ATEX and Class 1, Zone 1

- ATEX certified explosion proof
- Total Chlorine

Can be used for Total Chlorine measurements

- Able to operate in ambient temperatures up to 55°C
- Low operating costs

Low reagent use translates into low operating cost

Simple operation

Designed for unattended operation up to 90 days

- Colorimetric DPD chemistry
- Cycle times

Cycle times can vary between 60 seconds to 10 minutes

• Alarms

User selectable alarms for sample concentration

- Ballast water treatment, drinking water, wastewater and more
- 4-20mA and RS-485 with modbus
- USEPA accepted DPD method of analysis for measuring Total Residual Chlorine
- Extended range to 15ppm (option) ±10% accuracy



Ordering Information

PART NUMBER	DESCRIPTION
28031	CLX-Ex Online Chlorine Residual Monitor, 240VAC, for Total Chlorine, with operating manual. Reagents must be purchased separately.

Accessories

PART NUMBER	DESCRIPTION
09950Ex	Replacement tubing/cuvette kit

Reagents

PART NUMBER	DESCRIPTION
09991	Total Chlorine Reagent for CLX-Ex - 12 Month Supply (based on estimated BWTS operational cycles)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



Specifications

Measurement Range:0-10 mg/L or 0-15 mg/L (optional high range)Cycle Time:User Selectable: 60 seconds to 10 minutesAccuracy: $\pm 5\%$ of reading or $\pm 3 \text{ mg/L}$ (PPM) whichever is

greater for range of 0-6.0 mg/L (PPM)

±10% of reading from 6.01-10.00 mg/L (PPM)

Resolution: 0.01 mg/L (PPM)

Display:Multi-line liquid crystal backlit displayAlarms:One NO relay contact 120-240VAC 2AAnalog Output:Powered 4-10mA, 600Ω drive, isolatedCommunications Port:Bi-directional RS-485 with Modbus

Water Pressure: Integral pressure regulator 0.34 bar (5.0 PSI) to

10.3 bar (150 PSI)

Flow Rate to Waste: 200 to 400 ml/min

Operating Temperature: 0°C to 55°C (32°F to 131°F)

Wetted Materials: PVC, Borosilicate Glass, Reslyn (FFKM), Viton®

(FKM), Polypropylene, 316 Stainless Steel,

Acetal, Noryl®, Silicone

Sample Temperature

Range:

 0°C to 55°C (32°F to 131°F)

Power Supply: 100 to 240VAC, 47-63 Hz, 250VA **Insulation Rating:** Double Insulated, Pollution Degree 2,

Overvoltage Category II

Environmental Altitude up to 2000 meters. **Conditions:** Up to 95% RH (non-condensing) **IECEx Hazloc Rating:** Ex pxb IIC T4 Gb 0° C \leq Ta \leq 55°C

Compressed Air: Water and oil free, -40°F (-40°C) Dew Point,

Particles <5u, ISA Grade Hydrocarbon Free. Full time clean dry air at 5.5 - 7 bar (80-101.5 PSI) @35 SLPM (1.2 SCFM) @ 20°C (68°F)

Max

Regulatory Compliance ETL Listed to UL 61010-1 Issued May 11

and Certifications: 2013 3rd Ed & ETL certified to CSA 22.2 No.

61010.0 issued May 11 2012, EN61326:2006

Shipping Weight: 27.2 kg (60 lbs) Reagents are shipped

separately

Shipping Dimensions: 93 cm x 62 cm x 32 cm

(36-1/2" x 24-1/2" x 12-1/2")

NORYL is a registered trademark of SABIC Innovative Plastics IP B.V.

Viton is a registered trademark of DuPont Performance Elastomers LLC.



A WATTS Brand

ES-HF-CLX-Ex 1951 © 2019 HF scientific