

## Engineering Specification

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_

# Dead Level® SP

## Deck Channel with Polypropylene Frame

### Specification

Watts Dead Level® SP deck channel system with 6" wide x 48" long (standard) UV stabilized talc-filled polypropylene frame and channels with integral 4" IPS threaded bottom outlet. System will be frame-anchored, with (specify) grating to suit DIN Class (specify) load rating. System to include frame connectors, grate lock-downs, and construction covers. System can be specified in 1' increments. Installation to be performed in accordance with manufacturer's instructions and recommendations.


Call customer service if you need assistance with technical details.

| Options |                              |                          |
|---------|------------------------------|--------------------------|
| Suffix  | Description                  |                          |
| -FG     | Galvanized Steel Frame Guard | <input type="checkbox"/> |
| -FS     | Stainless Steel Frame Guard  | <input type="checkbox"/> |


| Grate Options |                                       |                                   |
|---------------|---------------------------------------|-----------------------------------|
| Suffix        | Description                           | Class                             |
| -BK           | Stainless Steel Brickslot             | Class E <input type="checkbox"/>  |
| -BR           | Decorative Bronze                     | Class B <input type="checkbox"/>  |
| -DI           | Ductile Iron                          | Class C* <input type="checkbox"/> |
| -DI-ADA       | Ductile Iron ADA                      | Class C* <input type="checkbox"/> |
| -FG           | Fiberglass                            | Class A <input type="checkbox"/>  |
| GDI           | Galvanized Ductile Iron               | Class C* <input type="checkbox"/> |
| -GP           | Galvanized Perforated                 | Class A <input type="checkbox"/>  |
| -GS           | Galvanized Slotted                    | Class A <input type="checkbox"/>  |
| -PP           | Polypropylene                         | Class C <input type="checkbox"/>  |
| -RGP          | Reinforced Galvanized Perforated      | Class C* <input type="checkbox"/> |
| -RGS          | Reinforced Galvanized Slotted         | Class C* <input type="checkbox"/> |
| -RSP          | Reinforced Stainless Steel Perforated | Class C* <input type="checkbox"/> |
| -RSS          | Reinforced Stainless Steel Slotted    | Class C* <input type="checkbox"/> |
| -SP           | Stainless Steel Perforated            | Class A <input type="checkbox"/>  |
| -SS           | Stainless Steel Slotted               | Class A <input type="checkbox"/>  |
| -SCI          | Solid Cast Iron                       | Class C* <input type="checkbox"/> |

\*Load Class E / ANSI Class XHD with Frame Guards

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



Typical Installation



Cross Section

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-DeadLevel-SP 2633

© 2026 Watts

