## **Engineering Specification**

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

# CO-190-PR-60

# PVC Adjustable Floor Cleanout with Integrated Level

### **Specification**

Watts Pronto!® CO-190-PR-60 PVC floor cleanout with anchor flange, post-pour adjustable round nickel bronze cover with integrated bubble level, leveling shims, and PVC socket outlet (standard).

Call customer service if you need assistance with technical details.

Pipe Sizing		
Suffix	Description	
2	2"(51) Pipe Size	
3	3"(76) Pipe Size	
4	4"(102) Pipe Size	

Options		
Suffix	Description	
-C	SS Membrane Clamp	
-6	Vandal Proof	

Outlet Type		
Suffix	Description	
NH	No Hub (MJ)	


Cover		
Suffix	Description	
PR5	5"(127) Dia., Nickel Bronze	
PR6	6"(152) Dia., Nickel Bronze	

#### **Chart A**

Cover Size	Min.	Max.	Load Rating
5"(127)	1 7/16"	2 15/16"	MD
6"(152)	1 7/16"	2 15/16"	LD

#### **Chart B**

Pipe Size	Std.60 PVC	No Hub
2"(51)	4 1/4"(108)	4 3/4"(121)
3"(76)	4 1/4"(108)	4 3/4"(121)
4"(102)	4 1/4"(108)	4 7/8"(121)



The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



**USA:** T: (800) 338-2581 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-CO-190-PR-60 2410