

Steam Products













watts.com

Introduction

Watts has been a leader in steam management technology and products since 1874. Steam products perform under severe conditions requiring high quality performance and quick in-line maintenance. We recognize the importance and value of designing high quality, longer service life features for these types of products. All our steam products are engineered to exceed established standards. This brochure describes the full line of Watts steam products designed to provide cost effective, efficient steam system solutions.

Table of Contents

General Information

Steam Traps
Selection Guide
A Guide to Steam Loss

Steam Traps

G, GH, MG, MGH – Thermostatic Radiator Steam Traps	6
QF – Quick-Fix™ Radiator Steam Trap Replacement Kits	7
WFT – Float & Thermostatic Steam Traps	8-9
WFTC, WFTK – F&T Steam Trap Cover Assemblies and Repair Kits	9
G, MG – Float & Thermostatic Steam Traps)-11
WIB – Inverted Bucket Steam Traps12	2-13
WTD 600 – Thermodynamic Steam Traps	. 14

Steam Safety Relief Valves

Fig. 31, 41, 41A – Bronze and Cast Iron Safety Relief Valves	15
315, 415 – Steam Safety Relief Valves	16
Figure 10 – Cast Iron Safety Relief Valves	16

Steam Process Regulators

127 – Process Steam Pressure Regulators	17
152A, 252A – Process Steam Pressure Reducing Valves	18
Capacity Charts	20

Steam Accessories

Teflon® is a registered trademark of E.I. Dupont de Nemurs Co, Inc.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

Steam Traps

Watts manufactures a variety of steam traps. To determine which trap is best for your application it is helpful to understand how each style of steam trap works. Below is a brief description of the operating principal of Thermostatic, Float & Thermostatic, Open Float & Thermostatic, Inverted Bucket, and Thermodynamic steam traps.

Thermostatic Radiator Traps

The thermostatic element in a radiator trap responds to temperature to open or close. At start-up when air and condensate are cooler the thermostatic element (diaphragm) contracts pulling the valve head off of the valve seat. The trap then opens and discharges air and cool condensate. As the condensate gets hotter the element expands driving the valve head into the valve seat closing the trap. The trap will stay closed until the condensate cools enough to contract the element and open the trap.

· These traps are recommended for radiators and convectors.

Float & Thermostatic Traps

Float & Thermostatic steam traps contain a sealed stainless steel thermostatic air vent and stainless steel ball float. The thermostatic air vent is open at start-up to discharge large volumes of air to the condensate return. As steam enters the trap body the air vent closes. The float is closed at start-up and stays in the closed position while steam is in the trap body. When the steam condenses, the hot condensate lifts the float moving the valve head off the seat opening the trap to discharge condensate. As condensate discharges steam enters the trap body, the float falls and drives the valve head into the valve seat closing the trap.

 These traps are designed to continuously discharge condensate in modulating conditions. Perfect for heat exchangers, air handling coils and steam main drip stations.

Open Float & Thermostatic Traps

Open Float & Thermostatic traps are designed to provide continuous air venting and condensate drainage using an open float, fail-safe design. In case of float failure, the trap will discharge condensate and air. The trap is designed with straight thru piping for easy installation.

Condensate fills the trap until it overflows into float. When the weight of the condensate overcomes the buoyancy of the float, the float begins to drop independent of the float valve head. The float continues to drop until the collar at the bottom of the valve stem engages the internal stop. At this impact point, the float falls to the bottom of the trap snapping the valve open. Condensate travels up the discharge tube, through the orifice and out the outlet port. The float will remain at the bottom with valve fully open so long as there is sufficient condensate entering the trap. As the discharge drains the float, buoyancy returns and the float begins to rise. The valve head is snapped closed into the valve seat by the velocity of the discharging condensate.

 These traps are ideal for low to medium pressure main drip applications as well as heat exchangers, air handling coils and other process applications.

Inverted Bucket Traps

Inverted Bucket Traps must be manually primed at start-up to create the water seal around the inverted bucket which allows the trap to operate. At start-up the trap is open and air and condensate enters the trap body. Air is discharged through a small vent on the top of the inverted bucket while condensate fills the trap body and is discharged through the valve seat located on the top of the trap body. When steam enters the trap body it collects in the inverted bucket. The buoyancy of the steam raises the inverted bucket which pushes the valve head into the valve seat, closing the trap. When the steam condenses the bucket is no longer buoyant causing the bucket to drop, opening the valve seat and allowing condensate to discharge to the condensate return line.

 These traps are ideal for use as main drip traps up to 250psi and on some steam equipment where minimal air venting capability is acceptable.

1









Thermodynamic Traps

At start-up, air and condensate under pressure raise the disc off of the valve seat opening the trap allowing discharge into the condensate return line. Hot condensate flashes to steam as it goes through the trap body. The velocity of the flash steam creates a lower pressure area under the disc causing the disc to seat. The pressure of the flash steam in the cap keeps the disc on the valve seat, closing the trap. The trap remains closed until the flash steam condenses allowing system pressure to raise the disc off of the valve seat.



• These traps are ideal for use as high pressure main distribution line traps from 75-600psi.

Steam Trap Selection Guide

Main Drip Applications

A main drip trap should be used every 100-150 feet of straight piping run. Traps should be used at each change of piping elevation and at risers as well as in front of expansion loops. The condensate load in a typical main drip application is small. It is unusual for main drip steam traps to be larger than ³/₄" (20mm).

PSI Range	Applicable Products
0-75psi	WFT, WIB
76-125psi	WTD 600, WFT, WIB
126-250psi	WTD 600, WIB
251-600psi	WTD 600

Typical Steam Main Drip Station



Size of Steam Main	Collection Leg Diameter A	Length C of collection leg Automatic Start Up:
¹ ⁄ ₂ " to 4" (13 to 102mm)	Same as main	Length to be 28" (711mm) or more
5" (127mm) & larger	2 to 3 pipe sizes smaller than main, but never small- er than 4" (102mm)	Supervised Start Up: Length to be 1 ¹ / ₂ times steam main diameter, but never shorter than 8" (203mm).

Process Applications

Process Applications include the following: heat exchangers, air handling coils, pre or reheat coils, unit heaters, cooking kettles and absorption chillers. Use WFT traps, sized at full load at 1/4 psi differential.

You Need to Know the Following to Properly Size a Process Trap:

- Steam load in #/hr
- Maximum system pressure
- Application (back pressure, lift to overhead returns or vacuum)



Pressure Reducing Applications



Pressure Reducing Valve Station

A Guide to Steam Loss

Faulty Steam Traps Are Leaking Money

The constant drive for energy conservation combined with the continual rise in energy costs has motivated colleges, universities, hospitals and other large facilities throughout the U.S. to become more aware of energy waste. In spite of this, institutions often overlook one particular area: the steam system. This is because steam systems appear to be functioning well. This perception may be misleading because the steam system may still be wasting significant amounts of energy and money. The problem - a well designed and properly installed steam system is inherently efficient and forgiving of bad maintenance practices. Thus, small defects can go unnoticed, while efficiency gradually degrades. Meanwhile, the accompanying increase in operating cost is easily lost in the overall costs of operating a facility.

Looking For The Sources of Leakage

Steam traps are perhaps the single major source of steam loss. This is because there are so many of them on a system and because they connect directly to the condensate return system. In large systems, individual traps may fail with little significant impact. But the collective waste of several faulty traps can push the cost of energy out of sight.

Problems with Vacuum Return Systems

In the condensate return system, steam injected by a leaking steam trap can cause severe operational problems by raising the temperature and the pressure of the return system. This can be particularly troublesome if a vacuum return system is used because it is virtually impossible to maintain a vacuum with steam leaking into the return lines. Proper steam and condensate circulation through the entire system is hampered or prevented. Operators try to restore the proper circulation by raising the pressure in the boiler, consuming more energy and driving up operating costs. So, if your system shows a loss of vacuum or pressure at the vacuum pump, it is a signal that steam is coming directly from the supply section into the return section.

Using a Condensate Pump

In systems using a condensate pump only, steam escaping into the condensate return line raises the condensate temperature to a point where it cannot be handled by the centrifugal condensate pump. Cavitation, noise and pump seal leaks are imminent if condensate temperatures are not brought to a reasonable level. In such cases, the pump simply cannot return the condensate to the boiler. Excessive temperatures at the condensate pump can be detected by noting the character of the discharge at the pump vent. With temperatures in the proper operating range (less than 190°F), there should be no noticeable discharge from the vent. An occasional wisp of vapor is acceptable.

Figuring Loss in Dollars and Cents

How much can leaking traps cost in wasted energy? It depends on the system's steam pressure (psi), the cost of the steam, and the number of traps involved. The example illustrated on the graph on page 5 indicates that one 1/4" orifice on a 2psi system could cost the owner \$478.80/trap every year. An older steam system used on a large campus could easily incorporate a hundred or more such traps.

General Information



Steam Loss through Trap Orifices at Various Steam Pressures

If you know the size of the orifice that is leaking steam and your particular system's pressure (psi), you can determine what the leak is costing you in wasted energy by using the graph above. For example, take a ¹/₄" (0.250 in.) orifice on a 2psi system. Find 0.250 on the vertical axis labeled Orifice Diameter (inches). Read horizontally to the 2psi steam pressure line. Then read vertically downward to "steam loss rate line" and determine steam loss rate at 19 lbs./hour. Steam costs approximately \$5.00/ per 1,000 lbs for steam generated in a highly efficient boiler plant to \$15.00 per 1,000 lbs. for purchased district steam. For the example cited, let's assume the steam cost at \$5.00/1,000 lbs. Also assume an operating period of 24 hours per day, 7 days a week, through a 7-month heating season (approximately 30 weeks.)

Total Operating Hours = 24 hours x 7 days/week x 30 weeks/year = 5,040 hours.

Now, Total Steam Loss = 5,040 hours x 19 lbs./hour = 95,760 lbs. of steam.

Thus, the Total Annual Cost = 95,670 lbs. x \$5.00 / 1,000 lbs. = \$478.80/year.

So, if: 1) your system pressure is greater than 2psi; 2) the orifice used on your system is larger than the $\frac{1}{4}$ " cited above; 3) there is more than one trap on the system; and, 4) you are paying more than \$5.00/1,000 lbs of steam – it's costing you real money to neglect your steam system, thus it is important to properly maintain your steam system.

*This information is based on an article written for the publication, American School & University, 6/92.

Series G, GH, MG, MGH

Thermostatic Radiator Steam Traps

For operating pressures up to 65psi (4.5 bar) Sizes: $\frac{1}{2}$ " – 1" (15 – 25mm)

Series G, GH, MG, MGH Thermostatic Radiator Steam Traps are designed to remove condensate, air and non-condensable gases from heating systems. The balanced pressure duplex phosphor bronze diaphragm is a highly sensitive modulating unit thermally programmed to provide accurate steam conserving operation. Available in a choice of various body patterns including angle, straightway, left hand corner, right hand corner, vertical and vertical double union.

Features

- Rugged brass construction with union inlet. Duplex phosphor bronze diaphragm sensitive within 3°F
- Hardened stainless steel valve
- Stainless steel valve seat
- Diaphragm and seat both replaceable
- Uniform operation within pressure range
- Superior operation under highest vacuum
- Each trap factory tested
- Standard patterns in 1/2", 3/4", and 1" (15, 20, 25mm)

For additional information, request literature ES-G/GH/MG/MGH.





Corner Pattern 1GLHC, 1GRHC



Applications

Models G and GH - 25" HG vacuum to 25psi (172 kPa)

- Low pressure and vacuum heating
- Convectors
- Unit Ventilators
- Radiators
- Fin pipes
- Drip points
- Air vents

Models MG and MGH - 25" HG vacuum to 65psi (448 kPa)

- Medium pressure heating equipment
- Process equipment
- Sterilizers
- Autoclaves
- Tracer lines
- Cooking equipment



1 VGDU



Vertical Pattern Single Union 1VG

MODEL	PATTERNS		TAP	PING			DIMENSIONS													WE	IGHT
		Inlet		Inlet Outlet			ale piece		_						_		_		•		
							A		3	(;)		E		F		G		
		in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kgs.
1GAP-1MGAP	Angle	1/2	15	1/2	15	27/8	73	1 1/8	29	1 ³ /16	35	13/8	35	-	-	-	-	-	_	1.2	.54
1GRHC-1GLHC	Corner	1/2	15	1/2	15	27/8	73	-	-	1 ³ ⁄16	35	13/8	35	9⁄16	14	25/8	67	15/8	41	1.4	.64
1GSW-1MGSW	Straightway	1/2	15	1/2	15	27/8	73	-	-	1 ³ /16	35	13/8	35	⁹ ⁄16	14	25/8	67	15/8	41	1.2	.54
1VG	Vert. S.U.	1/2	15	1/2	15	-	-	1 1/8	29	1 ³ ⁄16	35	13%	35	11 //8	48	4	102	25/8	67	1.4	.64
1VGDU	Vert. D.U.	1/2	15	1/2	15	-	-	2%16	65	1 ³ /16	35	13/8	35	11 //8	48	5 ³ /8	137	2 ³ / ₄	70	1.7	.77
3GH-3MGH	Angle	3⁄4	20	3⁄4	20	31/8	79	1%	35	1 ³ ⁄16	35	1%	41	-	-	-	-	-	-	1.5	.68
3GH-3MGH	Straight	3⁄4	20	3⁄4	20	31/8	79	-	-	1 ³ /16	35	1%16	40	3/8	10	23/4	70	11 //8	48	1.5	.68
5MGH	Angle	1	25	1	25	35/8	92	11/2	38	11/2	38	1 ¹¹ /16	43	-	-	-	-	-	-	2.5	1.13

Series QF Quick-Fix[™] Radiator Steam Trap Replacement Kits

Series QF Quick-Fix[™] Radiator Steam Trap Replacement Kits are used to repair old or obsolete radiator steam traps without the cost of replacing the steam trap body or expensive repiping. The stainless steel capsule and valve seat are designed as original equipment parts for many hard to find or obsolete radiator steam traps.

Remove the cover of the old steam trap and take out any remaining trap parts. Install the stainless steel Quick-Fix[™] seat and snap the stainless steel capsule onto the new seat. Replace the cover and the radiator steam trap has been repaired.

Contact Watts for any model radiator traps not listed below.

Traps with Replaceable Seats

Model No.	Manufacturer	1⁄2" Traps	3⁄4" Traps
QF-1	Warren Webster	02H, 02V, 502, 502V-1 702, 702V-1, 712, 902V	503, 703, 713
QF-2	Warren Webster	512, 512H-1, 512G-1 522, 522H, 522HB 712HB, 722HB	513, 533 523A, 523H-1**, 5236-1** 713HB, 733, 733HB 723A
QF-3	Warren Webster	902H	
QF-4	Warren Webster		913A, 913H
QF-5	Sarco TB25, TS25 T65 Erwel Illinois Trane Marsh	E, H, S65, TB25, TS25 T65 R30 1G B1* 1	E, H, S65 3GH
	Monash-Younker	30	
QF-6	Hoffman	17C	8C
QF-14	Marsh		2-4, 2-7
QF-15	Sterling	7-50A	
QF-16 Dunham-Bush	Trane	TH2A	B3

Traps with Integral Seats

QF-7	Dunham-Bush Trane	1B, 1C, 1R, V18 B2	
	Sarco		T25
QF-8	Sarco	T25	
	Hoffman	8	
QF-9	Illinois	1T, 2T	
QF-10	Barnes & Jones	122A, 122S, 3045	
QF-11	Barnes & Jones		134A, 134S
QF-12	Trane	B1*	
QF-13	Trane		B3

Replacement Air Vents for F&T Traps (15 and 30psi)

ALL

Series FT ³/₄" - 2" 686/55AL ³/₄" - 1"

ALL

Replacement Thermal Capsule Only

Sarco

Trane

QFC-10 ALL * Except vertical models

QF-25

QF-26

** Old style omits "-1" from symbol. For traps built since 1931 only.

For additional information, request literature ES-QF.

Quick, Easy installation

2.

З.



Install seat adapter, then snap capsule onto it.



Once the Quick-Fix $^{\rm TM}$ kits are installed, most subsequent trap repairs require only replacement of the capsule, which is the same for all trap kits.



Series WFT

Float & Thermostatic Steam Traps

For operating pressures up to 125psi (8.6 bar) Sizes: $\frac{3}{4}$ " – 2" (20 – 50mm)

Series WFT Float & Thermostatic Steam Traps are designed to provide continuous air venting and separate condensate draining with maximum efficiency and service. The "H" pattern body on all $\frac{3}{4}$ ", 1" (15, 30, 75, 125psi) and $\frac{1}{4}$ " (15, 30psi) has been designed to offer maximum installation flexibility. Four possible hookup combinations, combined with similar piping dimensions to other major manufacturers, make this the "universal" replacement trap. For larger sized traps, $\frac{1}{2}$ ", 2" (15, 30, 75, 125psi) and $\frac{1}{4}$ " (75, 125psi), the inlet and outlet taps are located in the cover. This design allowing for the larger capacities needed. Series WFT traps can also be serviced without disturbing system piping.



Features:

- Universal 4-port design
- All stainless steel internal components protect against erosion and corrosion
- Balanced pressure thermostatic element
- Extra-long life and dependable service
- Water hammer resistant
- Can be serviced without disturbing system piping

Applications:

- Unit heaters and other space heating equipment
- Heat exchangers/reboilers
- Air heating coils
- Steam main drips
- Process equipment







All 11/2", 2" WFT, 11/4" WFT-75, WFT-125



MODEL	SIZE	SIZE (DN) DIMENSIONS														IGHT
			A	1	E	3	0	;	D		E		E1			
	in.	тт	in.	mm	in.	mm	in.	тт	in.	тт	in.	тт	in.	mm	lbs.	kgs.
WFT-15	3/4	20	61/4	159	5½	140	35/16	84	3	76	5 ³ ⁄4	146	-	-	9	4.1
WFT-15	1	25	61/4	159	51/2	140	35/16	84	3	76	5 ³ /4	146	-	-	9	4.1
WFT-15	11/4	32	61/4	159	5 ³ ⁄4	146	35/16	84	3	76	5 ³ ⁄4	146	-	-	9.5	4.3
WFT-15	11/2	40	8 ½	216	4 ¹ / ₄	108	3	76	¹¹ / ₁₆	17	-	-	8 ³ / ₈	213	18	8.2
WFT-15	2	50	9 ¹³ /16	249	4 ¹⁵ / ₁₆	125	4 ¹⁵ / ₁₆	125	1⁄8	3	9 ¹ /8	231	-	-	26	11.8
WFT-30	3⁄4	20	61⁄4	159	51/2	140	3 ⁵ ⁄16	84	3	76	5 ³ ⁄4	146	-	-	9	4.1
WFT-30	1	25	61/4	159	51/2	140	35/16	84	3	76	5 ³ /4	146	-	-	9	4.1
WFT-30	11/4	32	61/4	159	5 ³ ⁄4	146	3 ⁵ ⁄16	84	3	76	5 ³ ⁄4	146	-	-	9.5	4.3
WFT-30	11/2	40	8 ¹ / ₂	216	4 ¹ / ₄	108	3	76	¹¹ / ₁₆	17	-	-	8 ³ / ₈	213	18	8.2
WFT-30	2	50	9 ¹³ ⁄16	249	4 ¹⁵ ⁄16	125	4 ¹⁵ ⁄16	125	1/8	3	9 ¹ /8	231	-	-	26	11.8
WFT-75	3/4	20	61⁄4	159	5½	140	35/16	84	3	76	5 ³ ⁄4	146	-	-	9	4.1
WFT-75	1	25	61⁄4	159	5½	140	35/16	84	3	76	5 ³ ⁄4	146	-	-	9	4.1
WFT-75	11/4	32	8 ¹ / ₂	216	4 ¹ / ₄	108	3	76	¹¹ / ₁₆	17	-	-	8 ³ / ₈	213	18	8.2
WFT-75	11/2	40	8 ½	216	4 ¹ / ₄	108	3	76	¹¹ /16	17	-	-	8 ³ / ₈	213	18	8.2
WFT-75	2	50	9 ¹³ /16	249	4 ¹⁵ / ₁₆	125	4 ¹⁵ / ₁₆	125	1/8	3	9 ¹ /8	231	-	-	26	11.8
WFT-125	3⁄4	20	61⁄4	159	51/2	140	3 ⁵ ⁄16	84	3	76	5 ³ ⁄4	146	-	-	9	4.1
WFT-125	1	25	61⁄4	159	5½	140	35/16	84	3	76	5 ³ ⁄4	146	-	-	9	4.1
WFT-125	11/4	32	8 ½	216	4 ¹ / ₄	108	3	76	11/16	17	-	-	8 ³ / ₈	213	18	8.2
WFT-125	11/2	40	8 ¹ / ₂	216	4 ¹ / ₄	108	3	76	¹¹ / ₁₆	17	-	-	83/8	213	18	8.2
WFT-125	2	50	9 ¹³ ⁄16	249	4 ¹⁵ ⁄16	125	4 ¹⁵ / ₁₆	125	1/8	3	9 ¹ /8	231	-	-	26	11.8

Steam Traps

Series WFT Float & Thermostatic Steam Trap Capacities Hot Condensate (lbs. per hr.)

	-	ze PT	PSIG															
Model	in	mm	Orifice	1⁄4	1/2	1	2	5	10	15	20	25	30	40	50	75	100	125
WFT-15	3⁄4"	20	.218	279	369	489	650	785	1000	1075								
WFT-15	1"	25	.218	279	369	489	650	785	1000	1075								
WFT-15	11⁄4"	32	.312	600	770	980	1240	1640	2000	2340								
WFT-15	11/2"	40	.500	1100	1700	2400	3300	5000	6600	7600								
WFT-15	2"	50	.625	2300	2800	3600	4650	6900	9000	10900								
WFT-30	3⁄4"	20	.218	279	369	489	650	785	1000	1075	1210	1300	1370					
WFT-30	1"	25	.218	279	369	489	650	785	1000	1075	1210	1300	1370					
WFT-30	11⁄4"	32	.228	375	500	690	910	1200	1500	1680	1800	1900	2000					
WFT-30	11/2"	40	.390	1000	1300	1700	2300	3400	4600	5500	6000	6600	7000					
WFT-30	2"	50	.500	1300	1800	2500	3400	5200	6800	7800	8600	9300	10000					
WFT-75	3⁄4"	20	.166	160	213	280	365	520	700	795	875	930	970	1120	1230	1450		
WFT-75	1"	25	.166	160	213	280	365	520	700	795	875	930	970	1120	1230	1450		
WFT-75	11⁄4"	32	.312	550	725	960	1300	1900	2650	3050	3400	3700	4000	4400	4750	5400		
WFT-75	11/2"	40	.312	550	725	960	1300	1900	2650	3050	3400	3700	4000	4400	4750	5400		
WFT-75	2"	50	.421	850	1100	1500	2000	3100	4150	4750	5200	5500	5800	6400	6800	7700		
WFT-125	3⁄4"	20	.125	100	135	175	230	330	415	500	585	620	685	750	830	970	1110	1190
WFT-125	1"	25	.125	100	135	175	230	330	415	500	585	620	685	750	830	970	1110	1190
WFT-125	11⁄4"	32	.246	400	520	680	890	1300	1700	2050	2300	2500	2700	3000	3200	3800	4200	4500
WFT-125	11/2"	40	.246	400	520	680	890	1300	1700	2050	2300	2500	2700	3000	3200	3800	4200	4500
WFT-125	2"	50	.332	550	675	880	1225	1950	2600	3000	3250	3500	3800	4200	4600	5500	6100	6600

For additional information, request literature ES-WFT.

Series WFTC, WFTK Float & Thermostatic Steam Trap

Cover Assemblies and Repair kits

Sizes: ³/₄" - 2" (20 - 50mm)

Series WFTC, WFTK Float & Thermostatic Steam Trap Cover Assemblies & Repair Kits are designed for use on Watts and select Spirax-Sarco F&T steam traps.

Features

- Quick, easy and economical
- Simplifies and standardizes inventory
- All stainless steel corrosion resistant internal parts

Models

- **WFTC** Cover assembly consists of a complete factory assembled unit which simply bolts on for ease of repair. No pipe connections need to be broken. There will be no reduction in the original trap's capacity.
- **WFTK** Designed for large traps that have piping connections into the cover plate. To avoid the "breaking" of piping connections, these kits are installed by removing the trap body. Each complete kit contains the thermostatic air vent, float, linkage, valve, seat and body gasket. These kits were designed to ensure ease of installation



WFTC

Series WFTC cover assemblies include the cast iron cover, condensate valve assembly, float and linkage, thermostatic vent in one factory assembled unit (A) and cover gasket (B).





WFTK

Series WFTK Repair Kits include condensate valve assembly - float and linkage (A), thermostatic vent and seat (B), and cover gasket (C).

Dimensions – Weights

MODEL	MANUFAC	TURERS	LINE	SIZE	WEI	GHT
	Model	Trap	in.	тт	lbs.	kgs.
3/4-WFTC-15	Spirax-Sarco	FT-15	3/4	20	3.0	6.6
3/4-WFTC-30	Spirax-Sarco	FT-30	3/4	20	3.0	6.6
1-WFTC-15	Spirax-Sarco	FT-15	1	25	3.0	6.6
1-WFTC-30	Spirax-Sarco	FT-30	1	25	3.0	6.6
1 ¹ /4-WFTC-15	Spirax-Sarco	FT-15	1 ¹ /4	32	3.0	6.6
11/4-WFTC-30	Spirax-Sarco	FT-30	1 ¹ /4	32	3.0	6.6
1 ¹ /2-WFTK-15	Spirax-Sarco	FT-15	1 ¹ /2	40	1.5	3.3
11/2-WFTK-30	Spirax-Sarco	FT-30	1 ¹ /2	40	1.5	3.3
2-WFTK-15	Spirax-Sarco	FT-15	2	50	1.5	3.3
2-WFTK-30	Spirax-Sarco	FT-30	2	50	1.5	3.3
2-WFIK-30	Spirax-Saicu	F1-30	2	50	1.0	3.3

For models of 75 or 125psi, please contact your Watts Representative for ordering information.

For additional information, request literature ES-WFTC/WFTK.

Series G, MG

Float & Thermostatic Steam Traps

For operating pressures up to 50psi (345 kPa)

Sizes: ³/₄" – 2" (20 – 50mm)

Series G, MG Float & Thermostatic Steam Traps are designed for use on modulating process equipment and as main distribution line drip traps. Series G Float & Thermostatic steam traps feature a straight through design for fast simple installation. Stainless steel valve head and seats provide long service life.

G, MG series steam traps have excellent air venting capability and discharge condensate at near to steam temperature so the steam space remains free of condensate providing improved steam system efficiency.

Features

- Fail safe In case of float failure, trap will discharge condensate and air; no unit freeze-up
- Air vent parts accessible without disturbing piping
- Inlet baffle breaks up water hammer; prevents damage to parts
- Snap action valve no wire-drawing or valve chatter
- Two moving parts no levers, hinges or pins to corrode or jam
- Straight-through connections saves installation time, labor, space, headroom
- Stainless valves and valve seats
- Seamless copper float no seams to develop leaks
 Uniform operations not affected by changes in load or pressures
- Condensate valve rotates ensures even wear, longer valve and seat life

Models

G-15 - 25" Hg to 15psi (103 kPa)

- MG-30 25" Hg to 30psi (207 kPa)
- MG-50 25" Hg to 50psi (345 kPa)

Applications

- Steam coils
- Unit heaters
- Drip points
- Heat exchangers
- Water heaters
- Absorption machines
- Unit ventilators
- Air handlers
- Make-up air coils
- Re-heat coils
- Jacketed kettles



MODEL	TAPPIN	G (NPT)								W	EIGHT			
			4	4	I	3	(С	I D			F		
	in.	тт	in.	тт	in.	тт	in.	mm	in.	тт	n.	тт	lbs.	kgs.
6G-15	3/4	20	4 ¹ /2	114	61/2	165	41/2	114	4 ¹⁵ /16	125	17⁄8	48	6	152
7G-15	1	25	5½	140	7 ¹ / ₂	191	5½	140	55%	143	2 ¹ /16	52	9	229
8G-15	11/4	32	5 ¹ /2	140	8	203	6	152	5½	140	2	51	12	305
91G-15	11/2	40	75%	194	113⁄4	298	8%16	217	9 ¹ / ₁₆	230	2 ³ /16	71	39	991
101G-15	2	50	9 ⁵ /16	237	13 ¹³ ⁄16	351	103/8	263	10 ¹⁵ ⁄16	278	23/8	60	59	1499
111G-15	2	50	103/8	264	15¼	387	115%	295	111/8	302	2 ³ ⁄4	70	85	2159
7MG-30	1	25	5½	140	7 ¹ / ₂	191	51/2	140	55/8	143	2 ¹ /16	52	9	229
8MG-30	11/4	32	5½	140	8	203	6	152	5½	140	2	51	12	305
91MG-30	11/2	40	75/8	194	113⁄4	298	8%16	217	9 ¹ / ₁₆	230	2 ³ ⁄16	71	39	991
101MG-30	2	50	9 ⁵ /16	237	13 ¹³ ⁄16	351	103/8	263	10 ¹⁵ /16	278	23/8	60	59	1499
111MG-30	2	50	103/8	264	15¼	387	115/8	295	111//8	302	2 ³ ⁄4	70	85	2159
6MG-50	3⁄4	20	4 ¹ / ₂	114	61/2	165	4 ¹ / ₂	114	4 ¹⁵ /16	125	11/8	48	6	152
7MG-50	1	25	5½	140	7 ¹ / ₂	191	5½	140	55/8	143	2 ¹ /16	52	9	229
8MG-50	11/4	32	5½	140	8	203	6	152	5½	140	2	51	12	305
91MG-50	11/2	40	75/8	194	113⁄4	298	8%16	217	9 ¹ / ₁₆	230	2 ³ ⁄16	71	39	991
101MG-50	2	50	9 ⁵ /16	237	13 ¹³ ⁄16	351	103/8	263	10 ¹⁵ /16	278	23/8	60	59	1499
111MG-50	2	50	103/8	264	15¼	387	115%	295	111 // 8	302	2 ³ ⁄4	70	85	2159



Maximum Trap Capacities

	Valve Seat	Pressure	1⁄4	1/2	1	2	5	10	15	20	30	50	75	100	125	150	175		
	Orifice	Differential																	
Model	Diameter	Lat. Ht. Value	969.8	969.3	968	966	961	952	945	939	929	912	895	881	868	857	847		
		Lbs. Cond./Hr.	70	100	140	200	210	220	230	The h			tinne						
³ ⁄4-6G-15		MBH	68	97	136	193	202	209	217				0	re expres			cou-		
		EDR	282	404	566	804	841	870	904		densate per hour at various pressure differentials. For ease of trap selection the tables also give the heating								
		Lbs. Cond./Hr.	175	250	350	500	525	550	575		value in MBH of the steam condensed. This is arrived at by								
1-7G-15	ards	MBH	170	242	339	483	505	524	543					rating					
	tand	EDR	708	1008	1413	2012	2104	2183	2263	Latent	t Heat Va	alue and	dividin	g by 1,00	0 to dete	rmine I	MBH.		
	**Capacities According to Recommended Shema Standards	Lbs. Cond./Hr.	425	600	850	1200	1260	1320	1280					rvice trap					
1¼-8G-15	hem	MBH	412	582	823	1159	1211	1257	1304					t Equival					
	Acco ad S	EDR	1717	2423	3428	4830	5045	5236	5434					ling the y 240 B					
	ies / ende	Lbs. Cond./Hr.	850	1200	1700	2400	2520	2640	2760		alent Dir			y 240 B	IU/ПІ./З	quare	FUUL		
1½-91G-15	acit	MBH	824	1163	1646	2318	2422	2513	2608	Exam		oornaa	iution.						
	Cap ecor	EDR	3435	4847	6857	9660	10091	10472	10868		•	for a Hr	nit Heat	er with a	heating	canaci	tv of		
	* @	Lbs. Cond./Hr.	1775	2500	3550	5000	5250	5500	5750					i line. A 2					
2-101G-15		MBH	1721	2423	3436	4830	5045	5236	5434	is des		J							
		EDR	7172	10096	14318	20125	21021	21817	22641			MB	H rating	, for sele	ction pur	poses =	= 2		
2-111MG-15	²¹ / ₃₂	Lbs. Cond./Hr.	2200	2900	3920	5200	7600	10100	12000					10 MBH. I					
		MBH	2133	2811	3795	5023	7304	9615	11340					d select t					
³ ⁄4-30-30*	5/32	Lbs. Cond./Hr.	175	235	315	420	570	670	825	935	1160			H rating e					
		MBH	170	228	305	406	548	638	780	878	1078			ual capa					
1-7MG-30	1/8	Lbs. Cond./Hr.	95	127	170	228	335	445	530	600	700			ndensate t Equivale					
		MBH	92	123	165	220	322	424	501	563	650			he correc		Παυιαι	UII		
1¼-8MG-30	5/32	Lbs. Cond./Hr.	156	210	280	375	550	740	870	980	1160]			e a api				
		MBH	151	204	271	362	529	704	822	920	1078								
1½-91MG-30	19/64	Lbs. Cond./Hr.	525	700	940	1250	1850	2450	2930	3300	3900								
		MBH	509	679	910	1208	1778	2332	2769	3099	3623								
2-101MG-30	11/32	Lbs. Cond./Hr.	670	890	1180	1580	2340	3120	3700	4150	4900								
		MBH	650	863	1142	1526	2249	2970	3497	3897	4552								
2-111MG-30	15/32	Lbs. Cond./Hr.	1300	1750	2340	3120	4600	6100	7200	8200	9700								
		MBH	1261	1696	2265	3014	4421	5807	6804	7700	9011		_						
³ ⁄4-6MG-50	3/32	Lbs. Cond./Hr.	52	69	92	122	180	240	285	320	380	470							
		MBH	50	67	89	118	173	228	269	300	353	429							
1-7MG-50	7/64	Lbs. Cond./Hr.	81	108	143	190	280	375	440	500	590	730							
		MBH	79	105	138	184	269	357	416	470	548	666							
1¼-8MG-50	1⁄8	Lbs. Cond./Hr.	102	138	182	245	355	475	565	630	750	920							
		MBH	99	134	176	237	341	452	534	591	697	839							
1 ¹ /2-91MG-50	15/64	Lbs. Cond./Hr.	360	480	640	860	1260	1680	2000	2250	2670	3300							
	0.1	MBH	349	465	620	831	1211	1599	1890	2113	2480	3010	_						
2-101MG-50	9/32	Lbs. Cond./Hr.	460	610	820	1100	1600	2140	2520	2841	3350	4150							
	01.	MBH	446	591	794	1063	1538	2037	2381	2667	3112	3785	_						
2-111MG-50	²¹ / ₆₄	Lbs. Cond./Hr.	630	850	1140	1520	2220	2950	3500	3950	4700	5800							
		MBH	611	824	1104	1468	2133	2808	3308	3709	4366	5290							

Pounds Condensate Per Hour, MBH, and Square Feet EDR

*Also available in $\frac{1}{2}$ " (15mm) pipe size

Note: The condensate capacities for GF or MGF traps are the same as shown for G or MG float and thermostatic traps and selection should be made in the same manner.

**Ratings are in accordance with the recommended standards adopted by the Steam Heating Equipment Manufacturers Association. Select trap directly from table for the lowest differential that may exist in the system. Traps may be applied directly and no safety factor need be applied.

For additional information, request literature ES-G/MG.

Series WIB

Inverted Bucket Steam Traps

For operating pressures up to 250psi (17 bar)

Sizes: ¹/₂" – 1" (15 – 25mm)

Series WIB Inverted Bucket Steam Traps are designed for reliable condensate removal on steam main line drips for system pressure up to 250psi. Series WIB Inverted Bucket Traps have an excellent reputation as a long lasting, rugged steam trap, naturally resistant to water hammer.

Features

- In-line connections
- Hardened stainless steel valve and seat
- Cast iron body construction; Class 250
- Stainless steel bucket
- Test plug
- Drain plug

Models

- **WIB 80** $\frac{1}{2}$ " $\frac{3}{4}$ " (15–20mm) for operating pressures up to 150psi (10 bar)
- **WIB 81** ½" 1" (15–25mm) for operating pressures up to 250psi (17 bar)

Pressure - Temperature

WIB 80

Maximum Allowable Pressure: 150psi (10 bar) Maximum Allowable Temperature: 406°F (208°C) Maximum Operating Pressure: 150psi (10 bar)

WIB 81

Maximum Allowable Pressure: 250psi (17 bar) Maximum Allowable Temperature: 406°F (208°C) Maximum Operating Pressure: 250psi (17 bar)

Applications

- Steam main drips
- Process applications requiring minimal air venting

SIZE (NF			A		MENSIONS 3	C	;	WEIGHT		
in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kgs.	
WIB 80										
1/2	15	5	127	81/8	206	31/4	83	5.5	2.5	
3/4	20	5	127	81/8	206	31/4	83	5.5	2.5	
WIB 81										
1/2	15	5	127	75/8	194	31/4	83	6	2.7	
3⁄4	20	5	127	75/8	194	31/4	83	6	2.7	
1	25	5	127	75/8	194	31/4	83	6	2.7	







WIB 81



Steam Traps

Maximum Trap Capacities - WIB 80

	RENTIAL		IFICE ize	Model
psi	bar	in.	<i>mm</i>	80
1/4	.02	3⁄16"	5	139
1/2	.03	3⁄16"	5	200
3/4	.05	3⁄16"	5	240
1	.07	3⁄16"	5	270
2	.14	3⁄16"	5	340
3	.21	3⁄16"	5	390
4	.28	3⁄16"	5	425
5	.35	3⁄16"	5	450
10	.69	3⁄16"	5	560
15	1	3⁄16"	5	640
20	1	3⁄16"	5	690
25	2	1⁄8"	3	460
30	2	1⁄8"	3	500
40	3	1⁄8"	3	550
50	3	1⁄8"	3	580
60	4	1⁄8"	3	635
70	5	1⁄8"	3	660
80	6	1⁄8"	3	690
100	7	#38	-	860
125	9	#38	-	950
130	9	#38	-	550
150	10	#38	-	570
180	12	#38	-	—
200	14	#38	-	_
225	16	#38	-	—
250	17	#38	-	—

DIFFEREN Pressu			Drifice	Mode
psi	bar	In.	mm	81
1/4	.02	1/4	8	191
1/2	.03	1/4	8	300
3/4	.05	1/4	8	395
1	.07	1/4	8	450
2	.14	1/4	8	590
3	.21	1/4	8	680
4	.28	1/4	8	750
5	.35	1/4	8	830
10	.69	1/4	8	950
15	1	1⁄4	8	1,060
20	1	3/16	5	880
25	2	3/16	5	950
30	2	3/16	5	1,000
40	3	5/32	4	770
50	3	5/32	4	840
60	4	5/32	4	900
70	5	5/32	4	950
80	6	1/8	3	800
100	7	1/8	3	860
125	9	1/8	3	950
130	9	7/64	2.7	780
150	10	7⁄64	2.7	810
180	12	7⁄64	2.7	850
200	14	7⁄64	2.7	860
225	16	#38	-	730
250	17	#38	-	760

Note: Capacities given are continuous discharge capacities in pounds of hot condensate per hour at differential indicated.

For additional information, request literature ES-WIB.

Series WTD 600

Thermodynamic Steam Traps

For operating pressures up to 600psi (41 bar) Sizes: $\frac{3}{2}$ " – 1" (10 – 25mm)

Series WTD 600 Thermodynamic Steam Traps are economical and compact, designed to efficiently drain steam mains, steam tracing lines, and small process equipment. The WTD 600 Steam Trap discharges condensate at near to steam temperatures, so the steam space remains free of condensate. Their tight shut-off feature ensures that valuable steam energy is not wasted. The WTD 600's hard-ened disc is the only moving part, assuring a long service life, easy low cost main-tainability, and improved steam system efficiency.



Features

- Inexpensive: low initial purchase price and lower maintenance costs than traps requiring expensive repair kits
- Compact design; light weight and easy to install. Provides longer service life with simple maintainability. The only moving part is the hardened stainless steel disc
- Rugged all stainless steel: resistant to water hammer, freezing, superheat and corrosion for extra long service life
- Audible discharge cycle: checking trap operation is simple and does not require any special devices
- Blast discharge of condensate: eliminates dirt build up and provides a tight shutoff, saving valuable steam energy

Applications

- Steam main drainage
- Superheat steam applications
- Steam tracing lines
- Freeze protection for outside applications
- Small process equipment

Pressure – Temperature

Maximum Operating Pressure: 600psi (42 bar) Maximum Operating Temperature: 800°F (427°C) Maximum Allowable Pressure: 600psi (42 bar) Maximum Allowable Temperature: 800°F (427°C)

										B
SIZI	E (DN)			DIMEN	SIONS			WE	EIGHT	
	. ,	A	A		В	(C			
in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kg.	
3/8	10	2	51	13⁄4	45	13⁄4	45	.8	.36	
1/2	15	2 ¹¹ /16	68	13⁄4	45	2"	51	1.2	.54	
3⁄4	20	2 ¹³ /16	71	25/16	59	27/16	62	1.8	.82	A
1	25	35/16	84	2 ¹ / ₂	64	21/8	73	3.1	1.41	

Maximum Capacity - Lbs./Hr. at Saturation Steam Temperature

Ν	PT							PS	IG (BAR)						
CON	NECTION	3.5	5	10	20	30	50	75	100	150	200	300	400	500	600
in.	тт	(0.24)	(0.34)	(0.7)	(1.4)	(2.1)	(3.4)	(5.2)	(6.9)	(10.3)	(13.8)	(20.7)	(27.6)	(34.5)	(41.8)
3/8"	10	180	185	190	200	215	245	305	370	500	610	790	960	1100	1250
1/2"	15	300	310	345	410	465	575	700	810	1000	1140	1410	1630	1830	2000
3⁄4"	20	405	420	470	550	640	810	1000	1160	1450	1670	2100	2430	2750	3050
1"	25	640	670	725	865	980	1200	1470	1750	2200	2600	3250	3780	4250	4700

For Kg./Hr. multiply by .454

For additional information, request literature ES-WTD.

Figure 31, 41, 41A

Bronze and Cast Iron Safety Relief Valves

Models

Figure 31 – ASME Section I

Figure 31 is a top guided, high capacity, full nozzle safety relief valve available in bronze or cast iron for over pressure protection of steam boilers with operating pressure from 5 to 250psi (.35 to 17 bar).

Figure 41 – ASME Section VIII

Figure 41 is a top guided, high capacity, full nozzle relief valve for over-pressure protection on unfired pressure vessels, steam pressure reducing valve stations and other steam service applications with operating pressure from 5 to 250psi (.35 to 17 bar).

Figure 41A – ASME Section VIII

Figure 41A is a heavy duty, high capacity safety relief valve for compressors, intercoolers, aftercoolers and receivers, air makeup units, gas burners, pneumatic conveying/elevating equipment, dryers and other pressure vessels and piping, handling air, gases and vapors to 250psi (17 bar) with temperature to 406°F (208°C)

Features

- Unitized bonnet/base design
- Rugged construction and 2-ring control
- Single Unit Cap and lifting lever

Figure 31, 41, 41A Bronze Safety Valves

	,	,			
	Inlet	VALVE SIZE Orifice	Out	tlet	NPT X Outlet
in	тт		in	mm	
1/2	15	D	3/4	20	NPT x NPT
3/4	20	D	3/4	20	NPT x NPT
3⁄4	20	E	1	25	NPT x NPT
1	25	E	1	25	NPT x NPT
1	25	F	11/4	32	NPT x NPT
1 ¼	32	F	11/4	32	NPT x NPT
11/4	32	G	11/2	40	NPT x NPT
1 ½	40	G	11/2	40	NPT x NPT
11/2	40	Н	2	50	NPT x NPT
2	50	Н	2	50	NPT x NPT
2	50	J	2 ¹ / ₂	65	NPT x NPT
2 ¹ / ₂	65	J	2 ¹ / ₂	65	NPT x NPT

Figure 31, 41, 41A Cast Iron Safety Valves

		-			
1 ½	40	J	2 ¹ / ₂	65	250 FLG x NPT
11/2	40	J	2 ¹ / ₂	65	NPT x NPT
2	50	J	3	80	250 FLG x NPT
2	50	K	3	80	250 FLG x NPT
2	50	K	3	80	NPT x NPT
2 ¹ / ₂	65	K	3	80	250 FLG x NPT
2 ¹ / ₂	65	L	4	100	250 FLG x NPT
2 ¹ / ₂	65	L	4	100	NPT x NPT
3	80	K	3	80	250 FLG x NPT
3	80	L	4	100	250 FLG x NPT
3	80	М	4	100	250 FLG x NPT
3	80	M	4	100	NPT x NPT
4	100	N	6	150	250 FLG/125 FLG
4	100	Р	6	150	250 FLG/125 FLG
6	152	Q	8	200	250 FLG/125 FLG
6	152	R	8	200	250 FLG/125 FLG



How to Order Watts Safety Relief Valves

You must consider five parameters in order to select the correct valve for your application.

1) What is the valve size needed?

Nominal pipe size (Inlet x Outlet)

2) What is the application?

- ASME Section IV for Low-Pressure Steam Service and Equipment up to 15psi. Use Series 315/415 or Figure 10. (See page 20 for more information.)
- ASME Section I for Steam Boilers up to 250psi (17 bar). Use Figure 31.
- ASME Section VIII for Steam Service and Equipment up to 250psi. Use Figure 41.
- ASME Section VIII for air, gas, and vapors up to 250psi (17 bar). Use Figure 41A.
- 3) What is the set pressure in psi?
 - Confirm set pressure with project engineer or boiler plant personnel.
 - Watts valves perform in the 5-250psi (.35-17 bar) range.
- 4) What lbs/hr capacity must the valve relieve?
 - Set pressure and orifice size determine valve capacity.
 - Orifice size is designated by the letter D through R and is determined by ASME standards.
- 5) What end connections are required?
 - NPT x NPT
 - Flange x NPT
 - Flange x Flange

For additional information, request literature PG-SSRV.

Series 315 & 415

Steam Safety Valves

For steam heating boilers with operating pressures up to 15psi (103 kPa)

Series 315, 415 ASME Section IV Rated Steam Safety Relief Valves have been developed to provide high quality dependable low cost protection for any low pressure steam heating equipment operating up to 15psi (103 kPa). This series features a bronze body and stainless steel spring. A top guided stem and a non-shock Teflon® disc-to-metal seat ensures positive shutoff.

Models

L - Low pressure setting

SC - Satin chrome finish

Features

- High capacity
- · Positive shut off
- Non-sticking Teflon[®] disc
- Seat located above drain
- NPT threaded male inlet x threaded female outlet (drain) connection

MODEL	SIZE	1	ASME STEAM		DI	MENSION	IS			WEIG	ΉT
			Discharge Capacity		В	D)	1	-	Í	
	in.	тт	lbs./hr. @ 15psi	in.	тт	in.	тт	in.	тт	lbs.	kg.
315-M1	³ ⁄4 X ³ ⁄4	20 x 20	375	2 ¹¹ /16	68	13/8	35	1 ¹ ⁄ ₄	32	.55	.24
415-M1	³ ⁄4 X ³ ⁄4	20 x 20	450	2 ¹³ /16	71	1 5⁄16	33	11/4	32	.70	.31
415-M1	1 x 1	25 x 25	643	31/8	78	1 ¹¹ /16	43	1%	41	.91	.41
415	1¼ x 1½	32 x 40	1265	43⁄4	121	23/8	60	21/8	54	2.00	.91
415	1½ x 2	40 x 50	1860	5 ⁷ /16	138	25/8	67	2 ⁵ /16	59	3.00	1.36

4 1 Ε

For additional information, request literature ES-315 or ES-415.

Figure 10

Cast Iron Safety Relief Valves

For Steam Heating Boilers with operating pressures up to 15psi (103 kpa)

Figure 10 valves are ASME Code Section IV valves designed for industrial and commercial low pressure steam heating boilers and associated equipment. Standard pressure settings for saturated steam service are 5 - 15psi (34 - 103 kPa). Available in seven sizes ranging from 3/4" x 1" to 3" x 3" (20 x 25 to 80 x 80 mm), connections are male NPT screwed inlet and female NPT screwed outlet. The cast iron body is rated at 15psi (103 kPa) at saturated steam temperature 250°F (121°C).

Features

16

- Tight shutoff
- Sharp popping and closing action
- High repeatability
- Valve inlet and body one integral casting

High Capacity Safety Valves – A.S.M.E. Section IV

MODEL	SIZE	(DN)				DIMEN		WEIGHT				
				A	E	1	0		[)		
	in.	тт	in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kg.
Fig. 10†	³⁄₄ x 1	20 x 25	2¼	57	3 ⁵ /16	84	1 ³ ⁄16	30	21/8	54	1	.5
Fig. 10*	1 x 1¼	25 x 32	3	76	4	102	13%	35	25/8	67	2	.9
Fig. 10*	1¼ x 1½	32 x 40	31/4	83	5	127	1 ¹⁵ /16	49	3	76	3	1.4
Fig. 10†	1½ x 2	40 x 50	33/8	86	51/8	130	2	51	37/16	81	4	1.8
Fig. 10‡	2 x 2 ¹ /2	50 x 65	4 ¹ / ₂	114	6 ¹¹ /16	171	2 ¹¹ /16	68	4	102	8	3.6
Fig. 10∆	2 ¹ / ₂ x 2 ¹ / ₂	65 x 65	51/4	133	83/8	213	4	102	43/8	111	14	6.4
Fig. 10‡	3 x 3	80 x 80	6	150	91⁄2	241	43/8	111	51/8	130	22	10.0

Ċ R D

Set At: †(12psi/82.7 kPa),*(10psi/68.9 kPa), (2(8psi/55.2 kPa), (5psi/34.5 kPa)









.... A

Series 127

Process Steam Pressure Regulators

Sizes: 1/2" - 4" (15 - 100mm)

Series 127 Process Steam Pressure Regulators are single seated, remote control, diaphragm type regulators, ideal for institutional, industrial and commercial applications. These valves feature stainless steel and nickel alloy seats and trim for either superheated or saturated steam service as well as outstanding maintenance features that make spring and diaphragm chamber assembly changes and adjustments a snap.

Features

- Stainless steel and nickel alloy seats and trim
- Outstanding maintenance features

Applications

- Main line and high capacity process regulation service
- Heating applications
- Dead-end service

Models

- **127SC** $\frac{1}{2}$ " 1 $\frac{1}{4}$ " (15 32mm), bonze body with composition disc for initial pressure up to 150 lbs.
- **127SS** ½" 3" (15 80mm), bonze body with stainless steel disc for initial pressure up to 250 lbs.
- **F127** 3" 4" (80 100mm), iron body with Flanged connections for initial pressure up to 125 lbs.



Typical Installation

Series 127 may be installed with the diaphragm above or below the line. It may also be installed in a vertical line. Pressure connections must always have a water seal.





		^								
MODEL	SIZE	(DN)				WEIGHT				
				A		3	(;		
	in	тт	in	тт	in	тт	in	тт	lbs.	kgs.
127	1/2	15	4	102	1	25	15	381	22.5	10.2
127	3⁄4	20	4	102	1	25	15	381	23	10.4
127	1	25	4 ¹ / ₄	108	11/8	29	15	381	23.5	10.7
127	11⁄4	32	4½	114	11/4	32	15½	384	24	10.9
127	11/2	40	5¼	133	11/2	38	15¼	387	28	12.7
127	2	50	6	152	13⁄4	44	15%	391	32	14.5
127	21/2	65	71⁄4	184	21/8	54	15¾	400	34	15.4
127	3	80	8	203	23/8	60	16½	410	40	18.1
F127*	3	80	8	203	33⁄4	95	16¾	425	42	19.0
F127*	4	100	12½	308	4 ½	114	16¾	425	84	38.1

*Iron body, flanged connections

Dimension "D" is 6", 8" or 10" (152, 203 or 254mm) depending upon reduced pressure range.

For additional information, request literature F-127.

Series 152A, 252A

Process Steam Pressure Reducing Valves

Sizes: ¹/₂" – 2" (15 – 50mm)

Series 152A, 252A Process Steam Pressure Reducing Valves are used to reduce steam pressure to the lowest possible steam pressure that provides the required temperature for each application. This series is a self contained, spring actuated, pressure reducing valve designed for all process pressure reducing applications.

Features

• Serviceable in line

• Standard sensitivity adjuster

Models

152A - Iron body for pressures up to 200psi (14 bar)

252A - Bronze body for pressures up to 300psi (21 bar)

152A-T or 252A-T – With Teflon[®] valve disc operating temperatures are 300°F at 300psi (140°C at 21 bar) and 400°F at 200psi (204°C at 14 bar).

152SS – Stainless steel body for pressures up to 300psi (21 bar) **152SST** – Stainless steel body, tight seating model for dead end service for pressures up to 300psi (21 bar) Adjusting Springs for reduced pressure ranges between 3 and 140psi (.21 and 9.8 bars)

Laminated Metal Diaphragm

Stainless Steel Disc and Stem Guide

Replaceable Stainless Steel Seat and Valve Disc.**

> Stainless Steel Strainer Screen

Sensitivity Adjuster

**When utilizing a Teflon® valve disc in the 152AT, the maximum operating temperature are 300°F at 300psi (149°C at 21 bar) and 400°F at 200psi (204°C at 14 bar).

-	00	Ŭ	LLO	11/4	LOO	L /4	
For addit	ional inforr	nation. rec	uest literatur	e ES-152A	. ES-152SS	S or ES-252A.	

SIZ	E (DN)				WEIGHT				
	A				C	D			
in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kg.
1/2	15	6	152	7	178	1 ¹⁵ ⁄16	49	11	4.99
3/4	20	6	152	7	178	1 ¹⁵ ⁄16	49	11	4.99
1	25	71/2	191	71/2	191	2 ³ ⁄16	56	20	9.07
11/4	32	71/2	191	71/2	191	2 ³ ⁄16	56	20	9.07
1 ½	40	9	229	111/4	286	2 ³ /4	70	40	18.14
2	50	9	229	111/4	286	23/4	70	40	18.14







Series 127, 152A and 252A

Process Steam Pressure Regulators

Sizing and Capacity Information

To provide the most efficient and economical steam service it is critical to properly size the pressure reducing valve. Do not size pressure reducing valves based on piping line size. Instead size the valve based on the required steam load, inlet pressure, and the desired reduced pressure. The smallest sized valve that will satisfy the peak demand of a specific application is the correct size. If the regulator is too large the seat and disc will get wire drawn, the reduced pressure will not maintain set point and will be uneven resulting in poor control, short valve service life, and excessive maintenance. If the valve is too small it will not provide enough steam to satisfy the application. Use the sizing charts below to choose the correct sized pressure reducing valve for your application.

How to Use Steam Capacity Charts

1. To find correct valve size when initial and reduced pressure and amount of steam (pounds per hour) are known.

In Chart 1 under the known initial pressure and opposite the required reduced pressure select the figure shown. Divide the amount of steam required by the figure. The quotient thus obtained is the valve coefficient. Select a valve size whose coefficient is equal to or next larger than this figure.

Example:

Initial pressure is	100 lbs.
Amount of steam	275 lbs. per hour
Reduced pressure is	45 lbs.

Under 100 and opposite 45 is the figure 5059

Co-efficient is 275 equals .046 5950

For Type 127 the nearest valve co-efficient in Table A is .065, which corresponds to a 1/2" valve. For Type 152A the nearest valve co-efficient in Table A is .085, which corresponds to a 3/4" valve.

Table A – Valve Co–Efficients for Steam

TYPE	1/2"	3⁄4"	1"	1¼"	1 ½"	2"	2 ¹ /2"	3"
127	.065	.147	.262	.409	.589	1.05	1.64	2.36
152A-252A	.024	.085	.120	.132	.187	.216	-	-

- **2.** To determine the valve size when the amount of radiation, initial and reduced pressure are given. Convert the radiation to pounds of steam by dividing the sq. ft. of radiation by 4. Then proceed as in 1.
- **3.** To determine size of valve necessary for steam coil heater in water storage tank when initial and reduced pressure are given and heater recovery capacity in gal. per hour is known.

Multiply cap. gal. per hr. by .93 for 80° rise per hr. Multiply cap. gal. per hr. by 1.16 for 100° rise per hr. Multiply cap. gal. per hr. by 1.62 for 140° rise per hr. Multiply cap. gal. per hr. by 1.74 for 150° rise per hr.

The resulting figure is pounds of steam, required. Determined valve size as shown in 1.

4. To determine the capacity of a valve when the initial and reduced pressures are known.

In chart 1 under the known initial pressure and opposite the known reduced pressure select the figure shown. Multiply this by the co-efficient for the size of the valve. The result is the cap. in lbs. steam per hr.

Chart 1 — Steam Capacity Chart

													INI	TIAL PF	RESSUF	E										
		10.64	20	30	40	50	60	70	80	90	100	110	120	130	140	150	160	170	180	190	200	210	220	230	240	250
	0	1360	1830																							
	5	1110	1000	2250																						
	10		1670	2200	2790	3350																				
	15			۷			3890	4430																		
	20			1980	V				4850																	
	25			1500	2590	V				5390	5950															
	30				2250	3180	V					6480	7020													
	35				1670	2900	3740	V					1020	7560	8110											
REDUCED PRESSURE	40					2480	3510	4300									9080									
RES	45					1830	3180	4100	V									9620	10150	10720	11240	11780	12130	12820	13360	13860
D D	50						2700	3820	4680	V																
S	55						1980	3430	4430	5240	V															
E	60							2900	4100	5020	5800	V														
	65							2120	3670	4730	5600	6360	V													
	70								3090	4360	5350	6180	6910	V												
	75								2250	3890	5020	5950	6740	7460	V											
	80									3260	4620	5660	6520	7300	8070											
	85									2370	4100	5300	6270	7110	7860	V										
	90										3430	4850	5950	6860	7680	8410	V									
	95										2480	4300	5550	6570	7460	8240	8950	V								
	100											3590	5070	6220	7180	8030	8800	9500								

Series 127 Standard

Reduced Pressure Range Chart

The table below shows minimum and maximum reduced pressure ranges obtainable with various selections of chamber diameters and adjusting spring, depending on supply pressures.

Size	Model								INIT	'IAL PR	ESSURE										
		2	5	5	0	7	5	1(00	12	25	1	50	1	75	2	00	2	25	2	50
Size	Model	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.
	206	14	25	19	50	20	75	21	100	22	104	23	105	24	106	25	107	26	108	27	109
	208	10	25	10	50	11	50	11	51	12	51	12	52	13	52	13	53	14	53	14	54
1/2"	108	3	17	3	17	4	18	4	18	5	19	5	19	6	20	6	20	7	21	7	21
	110	2	9	2	9	3	9	3	10	3	10	3	10	4	10	4	11	4	11	4	11
	206	13	25	20	50	22	75	24	100	26	108	28	110	30	112	32	114	34	116	36	118
	208	10	25	11	50	12	51	13	52	14	53	15	54	16	55	17	56	18	57	19	58
3⁄4"	108	2	17	3	18	4	19	4	20	6	21	7	22	8	23	9	24	10	25	11	26
	110	2	9	2	9	3	10	3	10	4	11	4	11	5	12	5	12	6	13	6	13
	206	13	25	-	50	24	75	26	100	29	108	31	110	34	113	36	115	39	118	41	120
	208	10	25	11	50	12	51	13	52	14	53	15	54	16	55	17	56	18	57	19	58
1"	108	3	17	4	18	5	19	6	20	7	21	8	22	9	23	10	24	11	25	12	26
	110	2	9	2	9	3	10	3	10	4	11	4	11	5	12	5	12	6	13	6	13
	206	13	25	23	50	26	75	29	100	32	112	35	115	38	118	41	121	44	124	47	127
41/11	208	14	25	15	50	16	55	17	56	18	57	19	58	20	59	21	60	22	61	23	62
1 ¹ ⁄4"	108	4	24	5	25	6	26	7	27	8	28	9	29	10	30	11	31	12	32	13	33
	110	1	9	2	10	3	11	4	12	4	12	5	13	6	14	7	15	7	15	8	16
	206 208	15 11	25 25	24 13	50 50	28 15	75	31 17	100 54	35 19	117 56	38 21	120 58	42 23	124 60	45 25	127 62	49 27	130 64	52 29	134 66
1½"	208	7	25 25	8	30	9	52 31	10	54 32	11	33	12	34	13	35	25 14	62 36	15	04 37	29 16	38
1 72	110	3	10	0 4	11	5	12	6	32 13	7	33 14	8	34 15	9	35 16	14	30 17	11	37 18	12	30 19
	206	16	25	25	50	31	75	36	100	42	115	47	120	53	126	58	133	64	137	69	142
	208	9	25	12	50	15	53	18	56	21	59	24	62	27	65	30	68	33	71	36	74
2"	210	6	29	7	30	9	32	10	33	12	35	13	36	15	38	16	39	18	41	19	42
_	110	4	9	5	10	7	12	8	13	10	15	11	16	13	18	14	19	16	21	17	22
	206	11	25	27	50	35	75	42	100	50	118	57	125	65	133	72	140	80	148	87	155
	208	11	25	15	50	19	54	23	58	27	62	31	66	35	70	39	74	43	78	47	82
2 ¹ /2"	210	7	25	9	30	12	33	14	35	17	38	19	40	22	43	24	45	27	48	29	50
	110	4	10	6	12	9	15	11	17	14	20	16	22	19	25	21	27	24	30	26	32
	206	18	25	30	50	40	75	50	100	60	120	70	130	80	140	90	150	100	160	110	170
	208	12	25	18	50	24	56	30	62	36	68	42	74	48	80	54	86	60	92	66	98
3" – 4"	210	8	25	11	32	15	36	18	39	22	43	25	46	29	50	32	53	36	57	39	60
	110	5	11	8	14	12	18	15	21	16	28	20	31	26	32	29	35	33	39	36	42

Note: Consult factory for special ranges below those shown, providing initial pressure, reduced pressure and valve size.

Quick Reference Capacity Chart for Average Conditions

					INITIAL PR	ESSURE / REDL	ICED PRESSUR	E			
Model		Size	FROM 50	FROM 75	FROM 100	FROM 125	FROM 150	FROM 175	FROM 200	FROM 225	FROM 250
	in	mm	UP TO 20	UP TO 35	UP TO 50	UP TO 60	UP TO 70	UP TO 80	UP TO 90	UP TO 100	UP TO 125
					MAXIMUM CAPA	ACITIES IN LBS.	OF STEAM PER	HOUR			
127	1/2	15	218	302	387	474	555	643	731	811	900
127	3⁄4	20	492	682	875	1072	1255	1454	1653	1834	2037
127	1"	25	878	1216	1560	1911	2237	2591	2946	3268	3631
127	11/4	32	1370	1898	2436	2984	3493	4045	4599	5102	5668
127	11/2	40	1973	2733	3508	4297	5030	5825	6623	7348	8163
127	2"	50	3518	4872	6253	7660	8967	10385	11807	13099	14553
127	2 ¹ / ₂	65	5494	7610	9766	11964	14006	16220	18442	20459	22730
127	3"	80	7906	10950	14054	17216	20154	23440	26538	29441	32709
127	4"	100	8301	11497	14756	18076	-	-	-	-	-
252A-152A	1/2	15	80	111	143	175	205	237	270	299	332
252A-152A	3⁄4	20	285	394	506	620	726	841	956	1060	1178
252A-152A	1"	25	402	557	715	875	1025	1186	1349	1497	1663
152A	11/4	32	442	613	786	962	1127	1305	1484	1646	1830
152A	1½	40	665	870	1120	1355	1600	1950	2230	2460	2725
152A	2"	50	765	1000	1285	1490	1840	2242	2564	2829	3134

Example; Initial pressure is 100 lbs. reduced pressure is 50 lbs. and capacity required is 1500 lbs. of steam per hour. By referring to the proper initial reduce pressure column (100 to 50) 1560 lbs. per hour is closest to Required Capacity and corresponds to a Type 127 Valve, Size 1". **Note:** For reduced pressures above those shown for each initial pressure column, refer to Detailed Capacity Table.

Series 142

Process Boiler Water Feeders with direct feed through float chamber

Series 142 Process Boiler Water Feeders are for use on pressing machines and other small process boilers when feed through float chamber is permissible. This series comes standard with direct feed through float chamber.



Process Boiler Water Feeders with external water feed connectors

Series 144 Process Boiler Water Feeders are for use on pressing machines and other small process boilers. Water is fed automatically as needed to maintain the correct operating level in the boiler. The simple construction of the feed valve permits quick and easy cleaning should it become fouled by dirt in the water supply. This series comes standard with external water feed connections.

Pressure Ratings

WSP: 100psi (7 bar) WOG: 125psi (8.75 bar) Steam Pressure: Max. 100psi (7 bar) Water Pressure: Max. 125psi (8.75 bar) Water pressure must be at least 10psi (69 kPa) higher than steam pressure





For Technical Assistance Call Your Authorized Watts Agent.

-			Telephone #	Fax #
	HEADQUARTERS: Watts Regulator Company	815 Chestnut St., North Andover, MA 01845-6098 U.S.A.	978 688-1811	978 794-1848
بر ع	Edwards, Platt & Deely, Inc.	271 Royal Ave., Hawthorne, NJ 07506	973 427-2898	973 427-4246
asi	Edwards, Platt & Deely, Inc.	368 Wyandanch Ave., North Babylon, NY 11703	631 253-0600	631 253-0303
North East	W. P. Haney Co., Inc. WMS Sales, Inc. (Main office)	51 Norfolk Ave., South Easton, MA 02375 9580 County Rd., Clarence Center, NY 14032	508 238-2030 716 741-9575	508 238-8353 716 741-4810
	wws sales, inc. (wall office)	9500 county Ru., clatence center, NY 14052	/10/41-90/0	/10/41-4010
Mid Atlantic	J. B. O'Connor Company, Inc. RMI	P.O. Box 12927, Pittsburgh, PA 15241 Glenfield Bus. Ctr., 2535 Mechanicsville Tpk., Richmond, VA 23223	724 745-5300 804 643-7355	724 745-7420 804 643-7380
andi	The Joyce Agency, Inc.	8442 Alban Rd., Springfield, VA 22150	703 866-3111	703 866-2332
_ <u>₹</u> _	Vernon Bitzer Associates, Inc.	980 Thomas Drive, Warminster, PA 18974	215 443-7500	215 443-7573
	Billingsley & Associates, Inc.	2728 Crestview Ave., Kenner, LA 70062-4829	504 602-8100	504 602-8106
	Billingsley & Associates, Inc. Francisco J. Ortiz & Co., Inc.	478 Cheyenne Lane, Madison, MS 39110 Charlyn Industrial Pk., Road 190 KM1.9 - Lot #8, Carolina, Puerto Rico 00983	601 856-7565 787 769-0085	601 856-8390 787 750-5120
유민	Mid-America Marketing, Inc.	203 Industrial Price, Birmingham, AL 35211	205 879-3469	205 870-5027
as	Mid-America Marketing, Inc.	1364 Foster Avenue, Nashville, TN 37210	615 259-9944	615 259-5111
ым	Mid-America Marketing, Inc.	5466 Old Hwy. 78, Memphis, TN 38118	901 795-0045	901 795-0394
	Smith & Stevenson Co., Inc. Harry Warren, Inc.	4935 Chastain Ave., Charlotte, NC 28217 1400 North Orange Blossom Trail, Orlando, FL 32804	704 525-3388 407 841-9237	704 525-6749 407 841-9246
	Watts Georgia	2861-B Bankers Industrial Drive, Atlanta, GA 30360	770 209-3310	770 447-4583
=	Dave Watson Associates Disney McLane & Associates	1325 West Beecher, Adrian, MI 49221 428 McGregor Ave., Cincinnati, OH 45206	517 263-8988 800 542-1682	517 263-2328 877 476-1682
North Central	BWA Company	17610 S. Waterloo Rd., Cleveland, OH 44119	216 486-1010	216 486-2860
	Mid-Continent Marketing Services Ltd.	1724 Armitage Ct., Addison, IL 60101	630 953-1211	630 953-1067
ZŐ	Soderholm & Associates, Inc.	7150 143rd Ave. N.W., Anoka, MN 55303	763 427-9635	763 427-5665
	Stickler & Associates	333 North 121 St., Milwaukee, WI 53226	414 771-0400	414 771-3607
	Hugh M. Cunningham, Inc.	13755 Benchmark, Dallas, TX 75234	972 888-3808	972 888-3838
South Central	HMC Sandia Group Mack McClain & Associates	13755 Benchmark, Dallas, TX 75234 4407 Meramec Bottom, Suite G, St. Louis, MO 63129	505 222-3134 314 894-8188	800 339-0191 314 894-8388
at s	Mack McClain & Associates, Inc.	1450 NE 69th Place, Ste. 56 Ankeny, IA 50021	515 288-0184	515 288-5049
လိပ္လ	Mack McClain & Associates, Inc.	15090 West 116th St., Olathe, KS 66062	913 339-6677	913 339-9518
	OK! Sales, Inc.	214-A NE 12th., Moore, OK 73160	405 794-5200	405 794-5250
	Delco Sales, Inc.	1930 Raymer Ave., Fullerton, CA 92833	714 888-2444	714 888-2448
<u> </u>	Delco Sales, Inc. Fanning & Associates, Inc.	111 Sand Island Access Rd., Unit I-10, Honolulu, HI 96819 6765 Franklin St., Denver, CO 80229-7111	808 842-7900 303 289-4191	808 842-9625 303 286-9069
Western	Hollabaugh Brothers & Associates	6915 South 194th St., Kent, WA 98032	253 867-5040	253 867-5055
es.	Hollabaugh Brothers & Associates	3028 S.E. 17th Ave., Portland, OR 97202	503 238-0313	503 235-2824
Š	P I R Sales, Inc. Preferred Sales	3050 North San Marcos Place, Chandler, AZ 85225 31177 Wiegman Road, Hayward, CA 94544	480 892-6000 510 487-9755	480 892-6096 510 476-1595
	R. E. Fitzpatrick Sales, Inc.	4109 West Nike Dr. (8250 South), West Jordan, UT 84088	801 282-0700	801 282-0600
	-		001 202 0100	001 202 0000
	Watts Industries (Canada) Inc. (Watts Regulator Co. Division)	5435 North Service Road, Burlington, Ontario L7L 5H7	905 332-4090	905 332-7068
	Con-Cur West Marketing, Inc.	71B Clipper Street, Coquitlam, British Columbia V3K 6X2	604 540-5088	604 540-5084
	D.C. Sales Ltd. D.C. Sales Ltd.	#10-6130 4th St. S.E., Calgary, Alberta T2H 2B6 16726 111 Ave, Edmonton, Alberta T5M 2S6	403 253-6808 780 496-9495	403 259-8331 780 496-9621
	GTA Sales Team.	Greater Toronto Area	888 208-8927	888 479-2887
	Hydro-Mechanical Sales, Ltd.	3700 Joseph Howe Drive, Suite 1, Halifax, Nova Scotia B3L 4H7	902 443-2274	902 443-2275
a	Hydro-Mechanical Sales, Ltd.	P.O. Box 1445 (Mailing), 297 Collishaw St., Suite 7 (shipping) Moncton, New Brunswick E1C 9R2	506 850 1107	506 859-2424
Canada	J.D.S. Sales Ltd.	4 Lancaster Street, St. John's, Newfoundland A1A 5P7	506 859-1107 709 579-5771	506 859-2424 709 579-1558
an	Les Ent. Roland Lajoie	6221 Marivaux, St-Leonard, QC H1P 3H6	514 328-6645	
U U	Les Ent. Roland Lajoie	23 du Buisson, Pont Rouge, QC G3H 1X9	418 873-2500	418 873-2505
	Mar-Win Agencies, Ltd. Northern Mechanical Sales	1333 Clifton St., Winnipeg, Manitoba R3E 2V1 P.O. Box 280 (mailing) 163 Pine St. (shipping), Garson, Ontario P3L 1S6	204 775-8194 705 693-2715	204 786-8016 705 693-4394
	Palser Enterprises, Ltd.	P.O. Box 28136 (mailing), 1885 Blue Heron Dr., #4,	103 033-21 13	100 000-4004
	• •	London, Ontario N6H 5L9	519 471-9382	519 471-1049
	RAM Mechanical Marketing Inc.	1401 St. John Street, Regina, Saskatchewan S4R 1S5	306 525-1986	306 525-0809
	RAM Mechanical Marketing Inc. Walmar Mechanical Sales	510 Ave M South, Saskatoon, Saskatchewan S7M 2K9 24 Gurdwara Rd., Nepean, Ontario K2E 8B5	306 244-6622 613 225-9774	
	EXPORT Hdqtrs.: Watts Regulator Co.	815 Chestnut St., North Andover, MA 01845-6098 U.S.A.		978 794-1848
0804	EA OIT HUYES. Watto heydiator ou.		570 000-1011	570754-1040





Water Safety & Flow Control Products

USA: 815 Chestnut St., No. Andover, MA 01845-6098; www.watts.com Canada: 5435 North Service Rd., Burlington, ONT. L7L 5H7; www.wattscanada.ca © Watts Regulator Co., 2008