# **tekmar**<sup>®</sup> Application Brochure

**Boiler Control 284** 





Multi-Staging Replaces: 06/13

The Boiler Control 284 obtains maximum efficiency from mixed boiler plants by taking the characteristics of each boiler into account along with the target water temperatures & outdoor temperature.

The 284 provides numerous control options beyond the applications featured in this brochure. For a complete list of settings, refer to the 284\_D Installation & Operation Manual.

- · Outdoor temperature reset
- Programmable schedules
- tekmarNet® 4 compatible
- · Control up to four boilers
- Condensing & non-condensing boiler groups
- · Modulating, single stage or two stage
- · Boiler isolation valves

- BACnet® IP or Modbus® communication
- Primary pump sequencing
- DHW priority
- Setpoint operation
- · Combustion air damper control
- · Energy, flow & pressure monitoring



Two single stage non-condensing boilers & two modulating condensing boilers are operated to provide a boiler target temperature for space heating, indirect DHW and setpoint loads. The boiler target temperature for the space heating load is determined from outdoor temperature reset.

#### Features:

- The boiler plant is sequenced to obtain maximum efficiency based on the boiler types & target temperatures. For detailed information about sequencing, rotation & staging, refer to the 284 D Installation & Operation Manual.
- A flow sensor is used for flow and energy monitoring.
- System includes a combustion air (C.A.) damper. Proving of C.A. damper via external C.A. proof (motor end switch).
- Boiler ΔT monitoring is available when using optional boiler outlet sensors (S6 to S9) & boiler inlet sensor (S5).
- Remote monitoring from the Internet is available through the tN4 Gateway 483.
- · Communication with a Building Automation System (BAS) is available using BACnet® IP or Modbus®.

#### Essential Source (#) Settings:

## ENABLE (1) = AUTO CONDENSE (1) = NO Boil TYPE (1) = 1STG ENABLE (2) = AUTO CONDENSE (2) = NO Boil TYPE (2) = 1STG

ENABLE (3) = AUTO
CONDENSE (3) = YES
Boil TYPE (3) = MOD
ENABLE (4) = AUTO
CONDENSE (4) = YES
Boil TYPE (1) = MOD

## **Essential System Settings:**

PLANT FLW = PUMP	
AUX RELAY = DMPR	
PUMP 1 = AUTO	
PUMP 2 = OFF	
IDHW MODE = ON	
IDHW LOCATION - Boil	

APP MODE = RSET

IDHW SENSOR = ON IDHW PRIM PUMP = OFF SETP MODE = ON


SETP PRIM PUMP = OFF


#### Legend


S1 = Outdoor Sensor S2 = Boiler Supply Sensor S3 = Boiler Return Sensor S4 = DHW Sensor S5 = Boiler Inlet Sensor S6-S9 = Boiler Outlet Sensors F1 = Flow Sensor P1, P2 = Primary Pumps P3-P6 = Boiler Pumps P7 = IDHW Pump P8 = Setpoint Pump


# DIP Settings: External Flow Proof / Off External C.A. Proof / Off Off / Exercise

Setback / Off









Four modulating condensing boilers are operated to provide an outdoor temperature reset boiler target for a space heating load.

#### Features:

- The boiler plant is sequenced to obtain maximum efficiency based on the boiler types & target temperatures. For detailed information about sequencing, rotation & staging, refer to the 284\_D Installation & Operation Manual.
- Dual primary pumps with a flow proof provide redundancy. Pumps can be sequenced with equal run-time rotation.
- Boiler ΔT monitoring is available when using optional boiler outlet sensors (S6 to S9) and boiler inlet sensor (S5).

#### **Essential Source (#) Settings:**

# ENABLE (1) = AUTO CONDENSE (1) = YES Boil TYPE (1) = MOD ENABLE (2) = AUTO CONDENSE (2) = YES Boil TYPE (2) = MOD

ENABLE (3) = AUTO
CONDENSE (3) = YES
Boil TYPE (3) = MOD
ENABLE (4) = AUTO
CONDENSE (4) = YES
Boil TYPE (4) = MOD

#### **Essential System Settings:**

APP MODE = RSET PLANT FLW = PUMP PUMP 1 = AUTO PUMP 2 = AUTO

#### **DIP Settings:**



External Flow Proof / Off
External C.A. Proof / Off

Off / Exercise


Setback / Off


#### Legend


S1 = Outdoor Sensor S2 = Boiler Supply Sensor S3 = Boiler Return Sensor S5 = Boiler Inlet Sensor S6-S9 = Boiler Outlet Sensors


P1, P2 = Primary Pumps

P3-P6 = Boiler Pumps









Four two-stage non-condensing boilers are operated to provide a fixed setpoint temperature for a dedicated DHW load. The DHW recirculation pump can optionally be operated on a schedule to save energy.

#### Features:

- The boiler plant is sequenced to obtain maximum efficiency based on the boiler types & target temperatures. For detailed information about sequencing, rotation & staging, refer to the 284\_D Installation & Operation Manual.
- Boiler ΔT monitoring is available when using optional boiler outlet sensors (S3 to S6) & boiler inlet sensor (S2).

#### **Essential Source (#) Settings:**

()	<b>3</b> -
ENABLE (1) = AUTO	ENABLE (3) = AUTO
CONDENSE (1) = NO	CONDENSE (3) = NO
Boil TYPE (1) = 2STG	Boil TYPE (3) = 2STG
ENABLE (2) = AUTO	ENABLE (4) = AUTO
CONDENSE (2) = NO	CONDENSE (4) = NO
Boil TYPE (2) = 2STG	Boil TYPE (4) = 2STG

#### **Essential System Settings:**

APP MODE = DDHW
PLANT FLW = PUMP
AUX RELAY = DHWR


#### **DIP Settings:**


External Flow Proof / Of
External C.A. Proof / Off
Off / Exercise


Setback / Off

#### Legend

S1 = DHW Sensor P1-P4 = Boiler Pumps S2 = Boiler Inlet Sensor P5 = DHW Recirculation Pump S3-S6 = Boiler Outlet Sensors







Two modulating condensing boilers are operated to provide heat for a space heating load. The boiler target temperature for the space heating load is determined from outdoor temperature reset and indoor temperature feedback provided by tekmarNet® thermostats. One of the boilers (boiler #4 output) also operates to provide heat for an indirect DHW load with priority over space heating.

#### Features:

- The boiler plant is sequenced to obtain maximum efficiency based on the boiler types & target temperatures. For detailed information about sequencing, rotation & staging, refer to the 284 D Installation & Operation Manual.
- Outdoor Temperature Reset saves energy by operating the boiler plant using the lowest possible temperatures. Lower water temperatures ensure modulating condensing boilers operate at maximum efficiency.
- Indoor Temperature Feedback compensates for heat loss or gain caused by the sun, appliances or occupant activity to improve system efficiency, comfort & response time.
- Boiler ΔT monitoring is available when using optional boiler outlet sensors (S6 & S7) and boiler inlet sensor (S5).
- Remote access options are available through the tN4 Gateway 482 or 483.
- The boiler outlet sensor S7 is required for indirect DHW operation.

Boil TYPE (4) = MOD

#### **Essential Source (#) Settings:**

# ENABLE (1) = AUTO ENABLE (3) = OFF CONDENSE (1) = YES ENABLE (4) = AUTO Boil TYPE (1) = MOD CONDENSE (4) = YES

ENABLE (2) = OFF

### **Essential System Settings:**

APP MODE = RSET PLANT FLW = PUMP PUMP 1 = AUTO PUMP 2 = OFF IDHW MODE = ON IDHW LOCATION = NEAR IDHW SENSOR = ON

#### Legend

S1 = Outdoor Sensor S2 = Boiler Supply Sensor S3 = Boiler Return Sensor

S4 = DHW Sensor

S5 = Boiler Inlet Sensor P4 = IDHW Pump S6, S7 = Boiler Outlet Sensors

P1 = Primary Pump

P2, P3 = Boiler Pumps


DIP Settings:


External Flow Proof / Off


External C.A. Proof / Off

Off / Exercise

Setback / Off







Two modulating non-condensing boilers are operated to provide a boiler target temperature for space heating and indirect DHW loads. The boiler target temperature for the space heating load is determined from outdoor temperature reset and indoor temperature.

#### Features:


Essential Source (#) Settings:

• The boiler plant is sequenced to obtain maximum efficiency based on the boiler types & target temperatures. For detailed information about sequencing, rotation & staging, refer to the 284 D Installation & Operation Manual.

**Essential System Settings:** 

- Dual primary pumps are operated through a Pump Sequencing Control 132 (#1).
- Dual IDHW pumps are operated through a Pump Sequencing Control 132 (#2).
- System includes combustion air (C.A.) damper. Proving of C.A. damper via external C.A. proof (motor end switch).
- A flow sensor and pressure sensor are used for monitoring flow, energy and gauge pressure.
- Boiler ΔT monitoring is available when using optional boiler outlet sensors (S6 & S7) & boiler inlet sensor (S5).
- Remote access options are available through the tN4 Gateway 482 or 483.

#### ENABLE (1) = AUTO Boil TYPE (2) = MOD APP MODE = RSET IDHW LOCATION = Boil CONDENSE (1) = NO ENABLE (3) = OFF PLANT FLW = PUMP IDHW SENSOR = ON Boil TYPE (1) = MOD ENABLE (4) = OFF AUX RELAY = DMPR IDHW PRIM PUMP = OFF ENABLE (2) = AUTO PUMP 1 = AUTO FLOW SENSOR = ON CONDENSE (2) = NO PUMP 2 = OFF PRES SENSOR = ON IDHW MODE = ON Legend **DIP Settings:** S1 = Outdoor Sensor S6, S7 = Boiler Outlet Sensors P5, P6 = IDHW Pump 🔳 🖴 / 🏊 S8 = Pressure Sensor S2 = Boiler Supply Sensor X1, X2 = Current Switches External Flow Proof / Off S3 = Boiler Return Sensor F1 = Flow Sensor (connected to 132 #1) External C.A. Proof / Off S4 = DHW Sensor P1, P2 = Primary Pumps X3, X4 = Current Switches Off / Exercise S5 = Boiler Inlet Sensor P3, P4 = Boiler Pumps (connected to 132 #2) Setback / Off 132 #2 132 #1 Indoor OOO Sensor C.A. ○○○ Array 084's 482 / 483 tekmarNet®4 C.A. Damper S2



Four modulating condensing boilers are operated to provide an outdoor temperature reset boiler target for a space heating load.

#### Features:

- The boiler plant is sequenced to obtain maximum efficiency based on the boiler types & target temperatures. For detailed information about sequencing, rotation & staging, refer to the 284\_D Installation & Operation Manual.
- Isolation valves are used with each boiler allowing for pump energy savings when the system is designed with primary pumps utilizing variable frequency drives (VFD's). The isolation valves must be of the spring return, normally open / fail open type.
- Dual primary VFD pumps with a flow proof provide redundancy. Pumps can be sequenced with equal run-time rotation.

#### **Essential Source (#) Settings:**

ENABLE (1) = AUTO

CONDENSE (1) = YES

Boil TYPE (1) = MOD

ENABLE (2) = AUTO

CONDENSE (2) = YES

Boil TYPE (2) = MOD

ENABLE (3) = AUTO

CONDENSE (3) = YES

Boil TYPE (3) = MOD

ENABLE (4) = AUTO

CONDENSE (4) = YES

Boil TYPE (2) = MOD

Boil TYPE (4) = MOD

#### **Essential System Settings:**


APP MODE = RSET PLANT FLW = VALV PUMP 1 = AUTO PUMP 2 = AUTO


#### **DIP Settings:**


External Flow Proof / Off
External C.A. Proof / Off
Off / Exercise
Setback / Off


#### Legend

S1 = Outdoor Sensor S2 = Boiler Supply Sensor P1, P2 = Primary Pumps M1-M4 = Boiler Isolation Valves









13 of 16

# **Notes**

# **Notes**

#### **Specifications**

#### The following are the recommended specifications for the Boiler Control 284

- The control shall be capable of sequencing up to four single stage, two stage or modulating boilers.
- The control shall be capable of operating combinations of condensing & non-condensing boilers.
- The control shall be capable of adjusting the boiler plant target to provide indirect domestic hot water heating with priority.
- The control shall have the ability to calculate the boiler plant target temperature based on outdoor temperature reset.
- The control shall have the ability to set the boiler plant target temperature using an adjustable setpoint.
- The control shall have the ability to set the boiler plant target temperature as directed by a BAS, BMS or EMS.
- The control shall have an adjustable warm weather shut down applied to outdoor temperature reset operation.
- The control shall be able to operate two primary pumps in standby mode.
- The control shall have the options of a proof demand input or a flow sensor input to prove flow for the primary pump.
- The control shall provide an alert output for flow proof, CA proof & no heat failures.
- The control shall be able to operate one primary pump & one domestic hot water pump during a domestic hot water call.
- The control shall communicate with Modbus<sup>®</sup>, BACnet<sup>®</sup> IP & tekmarNet<sup>®</sup> systems to provide remote monitoring & adjustment.
- The control shall have the ability to display the current temperature difference between the return temperature & the supply temperature,  $\Delta T$ .
- The control shall have the option to measure fluid pressure & flow rates.
- The control shall have an option to rotate the boilers & primary pumps based on the accumulated running hours.
- The control shall display the run time of the boilers & optionally, primary pumps.
- The control shall use proportional, integral & derivative (PID) logic when modulating the boilers.
- The control shall have the option to modulate the boilers sequentially or in parallel.
- The control shall have an adjustable minimum supply water temperature setting to help prevent condensation of flue gases & subsequent corrosion & blockage of the boiler's heat exchanger & chimney.
- The control shall have the option of an automatic differential calculation in order to prevent short cycling of the boilers.
- The control shall have the option to have all of the boilers operate a pump or an isolation valve.
- The control shall have adjustable post purge settings that allow the primary & boiler pumps / valves to run for a set period after the boiler has been shut off.
- The control shall have the option for fixed lead & fixed last boiler rotation.
- The control shall have the option to prove & operate a combustion air damper output.
- The control shall have an adjustable minimum inter-stage delay that can be set manually or calculated by the control.
- The control shall have the option of accepting a 0 10 V (dc) or 2 10 V (dc) input signal from an energy management system. with an adjustable offset.
- The control shall have three separate lockable access levels (Advanced, Installer, User) to limit the number of setting adjustments available to various users.
- The control shall have manual override options to test boiler & pump operation, suspend boiler plant operation, operate pumps for purging & operate the system with a maximum heat output.
- The control shall have the ability to display the current outdoor, boiler supply, outlet, return & inlet temperatures.
- · The control shall continually monitor the temperature sensors & provide an error message upon a control or sensor failure.
- During extended periods of inactivity, all pumps shall be periodically exercised to prevent seizure during long idle periods.
- The control shall include a setback schedule that can be used by the control itself or shared with other tN4 devices.
- The control shall have the option to operate as a tN4 system control with a tN4 boiler bus.
- The control shall display the current % modulation of each boiler, or the number of stages fired.
- The control shall include an adjustment for the cycle length if connected to a tN4 network.



tekmar Control Systems Ltd., A Watts Water Technologies Company. Head Office: 5100 Silver Star Road, Vernon, B.C. Canada V1B 3K4, 250-545-7749, Fax. 250-545-0650 Web Site: www.tekmarControls.com

