Submittal Package

Engineering Specification, Installation, Operation and Maintenance Series LFM513-5 — Large

Pump Control Valve with Mechanical Check Feature

Sizes: 20 and 24"

A WARNING




Read this Manual BEFORE using this equipment.

Failure to read and follow all safety and use information can result in death, serious personal injury, property damage, or damage to the equipment.

Keep this Manual for future reference.

A WARNING

Local building or plumbing codes may require modifications to the information provided. You are required to consult the local building and plumbing codes prior to installation. If the information provided here is not consistent with local building or plumbing codes, the local codes should be followed. This product must be installed by a licensed contractor in accordance with local codes and ordinances.



A WARNING

Need for Periodic Inspection/Maintenance: This product must be tested periodically in compliance with local codes, but at least once per year or more as service conditions warrant. All products must be retested once maintenance has been performed. Corrosive water conditions and/or unauthorized adjustments or repair could render the product ineffective for the service intended. Regular checking and cleaning of the product's internal and external components helps assure maximum life and proper product function.

If installed on a fire sprinkler system, all mechanical checks, such as alarm checks and backflow preventers, should be flow tested and inspected internally in accordance with NFPA 13 and NFPA 25.

Table of Contents	Page
Engineering Specifications	
ACV Schematic	2
Basic Valves	3
Standard Components	7
Optional Components	
Installation	15



Series LFM513-5 - Large

Pump Control Valve with Mechanical Check Feature

Full Port Ductile Iron Single Chamber Valve

Features

- Opens at adjustable rate on pump start-up
- Closes at adjustable rate on pump shut-off
- Limit Switch turns pump off when valve closes
- Built-in Mechanical Lift-Check Feature prevents flow reversal
- Solenoid equipped with Manual Operator

Standard Components

- 1 Main Valve M518 Dual Chamber
- 2 Four-Way Solenoid
- 3 Check Valve
- 4 Limit Switch
- 5 ACS Adjustable Closing Speed (Globe Valve)
- 6 AOS Adjustable Opening Speed (Globe with Check)
- 7 Pressure Gauges
- X Isolation Cocks
- Y Wye strainer

FLOW CLOSES VALVE COPENS VALVE

Options and Accessories

O L Dual Limit Switch

Operation

The Pump Control Valve is designed to minimize the surges associated with the starting and stopping of pumps. The valve slowly opens and closes as required to control pumping related surges. The pump starts and stops against a closed valve.

Pump start up: When the pump is signaled to start, the 4-Way Solenoid is energized and directs fluid and pressure into the power chamber (below the diaphragm), and relieves fluid and pressure from the cover chamber (above the diaphragm). The fluid and pressure relieved from the cover chamber is vented to atmosphere or available floor drain. The valve opens at an adjustable rate, gradually admitting pumping pressure into the distribution system. Rate of valve opening is controlled by the adjustable opening speed control, which restricts the speed at which fluid and pressure evacuate the cover chamber. The valve remains fully open during the pumping cycle.

Pump shutdown: When the pump is signaled to shut-off, the 4-Way Solenoid is de-energized, and directs fluid and pressure into the cover chamber (above the diaphragm), and relieves fluid and pressure from the power chamber (below the diaphragm). The fluid and pressure relieved from the power chamber is vented to atmosphere or available floor drain. The valve closes at an adjustable rate, gradually reducing pumping pressure. Rate of valve closure is controlled by the adjustable closing speed control, which restricts the speed at which fluid and pressure evacuate the power chamber. When the valve reaches the closed position, the limit switch is actuated, turning the pump off.

Emergency Closure: The valve is equipped with a Mechanical Check Feature, which acts independent of diaphragm position, and provides immediate closure when flow ceases.

Manual Operation: Engaging the Solenoid Manual operator simulates power to the solenoid, manually opening the main valve. Disengaging the Solenoid Manual operator returns the valve to the closed position.

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

M Series Basic Valves

Pump Control Valve with Mechanical Check Feature

Full Port Ductile Iron Single Chamber Basic Valve

This Watts Automatic Control Valve (ACV) is a full port, single chamber basic valve that incorporates a one-piece disc and diaphragm assembly. This assembly is the only moving part within the valve allowing it to open, close, or modulate as commanded by the pilot control system.

Watts ACV Main Valves are Lead Free. The Watts ACV piloting system contains Lead Free* components, ensuring all of our configurations are Lead Free compliant.

Globe Pattern Single Chamber Basic Valve (M100)

Standard Materials

Body and Cover: Ductile Iron ASTM A536

Coating: NSF Listed Fusion Bonded Epoxy

Lined and Coated

Trim: 316 Stainless Steel

Elastomers: Buna-N (standard)

Nut, Spring and Stem: Stainless Steel

Anti-Scale: Xylan Coated Stem and Seat (Optional)

Operating Pressure

150# Flanged = 250psi (17.2 bar) 300# Flanged = 400psi (27.6 bar)

Operating Temperature

Buna-N: 160°F (71°C) Maximum

Epoxy Coating**: 225°F (107°C) Maximum

** Valves can be provided without internal epoxy coating consult factory

Basic Valve Body Options



Globe Flanged

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Flow Data


	Valve Size - Inches	11/4	1½	2	2½	3	4	6	8	10	12	14	16	20	24
ted	Maximum Continuous Flow Rate Gpm (Water)	95	130	210	300	485	800	1850	3100	5000	7000	8500	11100	19600	28200
Suggested	Maximum Intermittent Flow Rate Gpm (Water)	119	161	265	390	590	1000	2300	4000	6250	8900	10800	14100	24500	35250
S	Minimum Flow Rate Gpm (Water)	3	5	6	9	15	16	17	25	55	70	190	400		315
ځ	CV Factor GPM (Globe)	26	26	48	75	112	188	387	764	1215	1734	2234	3131		7447
	CV Factor GPM (Angle)	26	27	57	91	125	207	571	889	1530	1945				

- Maximum continuous flow based on velocity of 20 ft. per second.
- Maximum intermittent flow based on velocity of 25 ft. per second.
- Minimum flow rates based on a 20-40 psi pressure drop.
- The C_v Factor of a value is the flow rate in US GPM at 60° F that will cause a 1psi drop in pressure.
- C_v factor can be used in the following equations to determine Flow (Q) and Pressure Drop (ΔP):

Q (Flow) = $C_v \sqrt{\Delta P}$

 ΔP (Pressure Drop) = $(Q/C_v)^2$

- The C_v factors stated are based upon a fully open valve.
- Many factors should be considered in sizing control valves including inlet pressure, outlet pressure and flow rates.
- For sizing questions including cavitation analysis consult Watts with system details.




Valve Cover Chamber Capacity - Dual

Valve Size - Inches 20 24 U.S. Gal 45 64.9 Liter 170.3 245.7


Valve Travel

Valve Size - Inches	2	0	24				
	in.	cm.	in.	cm.			
Travel - Inches	5.62	14.3	6.75	17.1			



Item	Description	Material					
1	150# Body	Epoxy Coated Ductile Iron - ASTM A536					
2	Dowel Pin	Stainless Steel 18-8					
3	Insert	Epoxy Coated Ductile Iron - ASTM A536					
3	Cover	Epoxy Coated Ductile Iron - ASTM A536					
4	Diaphragm	Buna-N					
5	Nut Lifting Eye	Steel					
6a	Flange Screws x4	Stainless Steel 18-8					
6b	3/4 Lock Washer	Stainless Steel 18-8					
6c	Flange 1½ NPT, 300 CL	Stainless Steel - UNS S30400					
6d	Gasket 1½ Pipe	Buna-N					
7a	Guide Cover Screws	Stainless Steel 18-8					
7b	Guide Cover	Stainless Steel - UNS S30400					
7c	0-Ring	Buna-N - 70 DURO					
8	Cover Bearing with 0-Ring	ASTM A276 UNS S30400, Buna-N					
9 - 10	Cover Stud, Hex Nut	ASTM A193 GRB7 Yellow Zinc PLT					
11	Flat Washer	Carbon Steel Zinc Plated					
12	Insert Gasket Seal	Buna-N					
13	Stem Nut with Set Screw	Stainless Steel ASTM A276 304; Stainless Steel - 18-					
14	Stem Nut Washer	Stainless Steel - UNS S30400					
15a - 15b	Upper Stem and Lower Stem	Xylan Coated Stainless Steel – UNS S30400					
16	Sleeve Bearing	Bronze - SAE 841					
17	Upper & Lower Diaphragm Washer	Ductile Iron ASTM A536 65-45-12					
18	0-Rings x2	Buna-N					
19	0-Ring	Buna-N					
20	Stem Bearing with 0-Rings	Brass; Buna N					
21	Retaining Ring	Stainless Steel 18-8					
22	0-Ring	Buna-N					
23	Disc Retainer	Epoxy Coated Ductile Iron – ASTM A536					
24	Stem Nut Washer	Stainless Steel 304					
25	Disc	Buna-N					
26	Disc Guide Plate with Screws	Stainless Steel - UNS S31600					
27	Seat with Seat Screws	ASTM A743 CF8M; Stainless Steel 18-8					
28	Seat 0-Ring	Buna-N					
29	Stem Nut with Screw	Stainless Steel ASTM A276 304; Stainless Steel - 18-8					






NOTICE

Installation: If unit is installed in any orientation other than horizontal (cover up) OR extreme space constraints exist, consult customer service prior to or at the time of order.

Dimensions



Valve Size	GIODE 150#		Globe 150#		Globe	300#	Cover To	Center	Port Si	ze NPT	Port Si	ze NPT	Shipping	Weights*
	Α		В		С		C D F		F					
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.		
20	52	1320.8	53%	1362.1	49½	1257.3	1½	38.1	1½	38.1	5803	2632.2		
24	61½	1562.1	63¼	1606.5	57¼	1454.2	1½	38.1	1½	38.1	8411	3815.2		

ACV Standard Components - Series LFM513-5 - Large

Model S4W

3-Way Solenoid

Size: 1/8" - 1/2" NPT

Model S4W are pilot system 4-way solenoids. The solenoids can control valves independently or in combination with other control circuit pilots or accessories. Product is available with a wide range of options including: voltage (24VDC, 24VAC or 120VAC), and a range of enclosures (general service to watertight to explosion proof).



Model S4W
Back View showing Ports A and B



Normal Position



Actuated Position



Model S4WFront View showing Ports P and E

Specifications

Body Material: Brass (standard)***

Elastomers: Nitrile (standard)

EPDM (optional) Viton™ (optional)

Voltage: 24VDC, 24VAC or 120VAC

Enclosure: General Purpose – NEMA 4 (standard)

Explosion Proof – NEMA 6, 6P, 7, 9 (optional)

Action: 4-Way Actuation

**Solenoid Action only. Main valve action (energize-to-open or energize-to-close) is dependent on the particulars of the pilot system.

***Brass solenoids are not lead free and it is illegal to use them in potable services in the United States such as drinking water, handwashing, food preparation, and dishwashing. However, brass solenoids may be used as a replacement component in a lead free Watts ACV main valve, as the wetted surface of a lead free Watts ACV main valve including installed brass solenoids contains less than 0.25% of lead by weight.

Viton $\ensuremath{^{\mathsf{TM}}}$ is a trademark of The Chemours Company FC, LLC

ACV Standard Components - Series LFM513-5 - Large


LEAD FREE*

Model CK

Check Valve

Size: 1/4" - 1" NPT

Model CK Check Valves are pilot line check valves. In typical applications these low cracking pressure in-line checks provide a hydraulic check feature to a pilot system. When the main valve outlet pressure exceeds inlet pressure, fluid is directed from the outlet to the main valve cover. This causes the main valve to close until inlet pressure is again greater than outlet.





Model LFCK

Specifications

Standard Material: Brass Housing and Body

Stainless Steel Indicating Rod

Optional Material: Stainless Steel Housing and Body Disc

Viton® (1/4" - 1/2") PTFF (1")

Pressure Rating: 400psi (27.6 bar)

Viton® is a registered trademark of DuPont Dow Elastomers.


*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Model 51


Single Limit Switch

The Model 51 Single Limit Switch provides visual indication of valve position, as well as remote electrical indication of "valve open" or "valve closed". The single pole double throw Micro-Switch can be connected to open or close an electrical circuit when the valve opens or closes.

The adjustable collar is normally set to contact the trip arm when the main valve is closed. The collar can be positioned on the stem by loosening the set-screw to actuate the switch at the desired point of valve travel.



Single Pole Double Throw Switch





Model LF51

Specifications

Body Material: Stainless Steel

Elastomers: Buna-N (standard)

EPDM (optional)
Viton™ (optional)

Enclosure: NEMA 1, 3, 4 and 13 General Purpose (standard)

NEMA 1,7 and 9 Explosion Proof (optional)

Electrical: Form C SPDT Switch

15 amp. 125, 250 or 480 VAC

½ amp. 125 VDC ¼ amp. 250 VDC ½" Conduit Connection

Viton™ is a trademark of The Chemours Company FC, LLC

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Parts List

Item	Description
1	Limit Switch
2	Bracket
3	Stem
4	Trip collar
5	Set Screw
6	Сар
7	Wiper Ring*
8	0-Ring*
9	Guide
10	0-Ring*
11	Polypak*
12	Locknut
13	Body
14	Pin
15	Coupling

*Included in Repair Kit

Series LF622F/FT/ UF/UFT

Lead Free* Bronze, Full Port Ball Valves

Size: 1/2" - 2"

Features

- The FEBCO Series LF622FT/LF622UFT available with tapped side outlet suitable for installation of pressure gauges or test cocks. LF622UF/UFT with Union Ends.
- Lead Free* construction to comply with Lead Free* installation requirements.
- Tee handle standard on ½" through 1¼" sizes (15mm 32mm).
- Lever handle standard on 1½" through 2" sizes (40mm 50mm).
- Full port design for low pressure drop.
- Pressure rated at 600psi (41.4 bar) WOG, (non-shock) ½"-2" (15mm – 50mm) (DN15-DN50) and 125psi (8.6 bar) saturated steam.
- Suitable for temperature from 0°F to +350°F (-18°C to 177°C) at 50psi (345 kPa).
- PTFE stem packing seal, thrust washer and seat.
- Plated carbon steel handle with vinyl insulator.
- Quarter-turn open or close operation. (Not intended for throttling applications.)
- Ideal for throttling and balancing applications of non-abrasive fluids where minimum flow is 20% to 100% of valve capacity.
- Low operating torque.
- · Adjustable stem packing gland.
- Bottom loaded, pressure retaining stem.





Series LF622UF

Series LF622FT

Options

LF622F: Full Port Thread x Thread Ball Valve
LF622FT: Full Port Thread x Thread Ball Valve with

Tapped Side Outlet

LF622 UF: Full Port Thread x Thread Ball Valve with (1)

Union End

LF622 UFT: Full port Thread x Thread Ball Valve with (1)

Union End with Tapped Side Outlet

Specification


Approved valves shall have bottom loaded pressure retaining stems, PTFE seats and full port. Valve shall be pressure rated at 600psi (41.4 bar) WOG (non-shock), 125psi (8.6 bar) saturated steam. Valve must conform to Federal Specification WW-V-35C, Type II, Composition, BZ, Style 3, End Connection A. The Lead Free* copper silicon alloy full port ball valves shall comply with state codes and standards, where applicable, requiring reduced lead content. Valve shall be a FEBCO Series LF622F.


Series LF622F/FT/UF/UFT

Lead Free* Bronze, Full Port Ball Valves

Size: 1/2" - 2"

Dimensions - Weights





Size: 1/2" - 2"

Size		Series LF622FT / UFT Dimensions											Weight									
	A A1 (union) B B1 (union) C									F		G		LF622FT		LF622UFT						
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.	lbs.	kgs.
1/2	23//8	61	31/2	79					31/8	79	17/16	36	1	25	5/8	16	1% - 27	n/a	.6	.3	.7	.3
3/4	25//8	67	3½	89					31/8	79	1%	41	11/4	32	3/4	19	% - 27	n/a	.8	.4	1.1	.5
1	31/8	79	4	102					3%16	91	2	51	11/2	38	¹³ / ₁₆	20	1 _% - 27	n/a	1.3	.6	1.6	.7
11/4	35/8	92	4%16	116					3%16	91	21/16	53	1 13/16	46	13/16	21	1/4 - 18	n/a	2.3	1.0	2.4	1.1
1½	37/8	99	5	129	8½	216	91/2	241			3	76	23/16	55	13/16	21	1/4 - 18	n/a	3.2	1.4	3.7	1.7
2	47/16	113	511/16	144	81/2	216	95//8	244			3½	89	23/4	70	¹³ / ₁₆	21	1/4 - 18	n/a	5.6	2.5	6.4	2.9

Size: 1/2" - 2"

Size		Series LF622F / LF622UF Dimensions													Weight				
	1	A	А	.1	В		B1		С		D		E		LF622FT		LF622UFT		
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.	lbs.	kgs.	
1/2	23/16	55	3	74					31/8	79	17/16	36	1	25	.6	.3	.7	.3	
3/4	2%	61	31/4	82					31/8	79	1%	41	11/4	32	.7	.3	1.0	.5	
1	27//8	73	33/4	96					3%16	91	2	51	11/2	38	1.3	.6	1.6	.7	
11/4	31/4	83	43/16	107					3%16	91	21/16	53	1 13/16	46	2.0	.9	2.4	1.1	
1½	3%	92	43/4	120	8	206	9	231			3	76	23/16	55	3.1	1.4	3.6	1.7	
2	43/16	106	5%	137	8%	213	911/16	246			3½	89	23/4	70	5.3	2.4	6.3	2.9	

Series LF777, LFS777

Wye-Pattern Lead Free* Bronze Strainers

Sizes: 1/4" - 4"

Series LF777, LFS777 Wye-Pattern Lead Free* cast copper silicon alloy Strainers are designed to protect system components from dirt, rust and other damaging debris in the piping system. This series features a solid retainer cap with gasket. The LF777 and LFS777 features Lead Free* construction to comply with Lead Free* installation requirements.

Features

- Lead Free* cast copper silicon alloy body
- Wye-pattern
- · Solid retainer cap with gasket

Models

LF777 $\frac{1}{4}$ " - 4" threaded connections **LFS777** $\frac{1}{2}$ " - 2" solder connections

Specifications

A wye-pattern Lead Free* cast copper silicon alloy strainer to be installed as indicated on the plans. The strainer must have a solid retainer cap with gasket. Strainer shall be rated to 400psi (27.6 bar) WOG @ 210°F (99°C); 125psi (8.6 bar) WSP @ 353°F (178°F) for sizes ½" – 3" and 300psi (20.7 bar) WOG @ 210°F (99°C); 125psi (8.6 bar) @ 353°F (178°C) for size 4". Lead Free* Wye-Pattern cast copper silicon alloy Strainers shall be constructed using Lead Free* materials. Lead Free strainers shall comply with state codes and standards, where applicable, requiring reduced lead content. Strainer shall be a Watts Series LF777 (threaded ends) or LFS777 (solder ends).

Materials

Body: Lead Free* cast copper silicon alloy

Retainer Cap: 1/4" – 4": Lead Free copper silicon alloy

Cap Seal: 1/4" - 3": EPDM O-Ring

4": Garlock® gasket

Standard Screen: 1/2" - 21/2": 304 stainless steel #20 mesh,

3": 3/64" (1.2mm) 304 stainless steel

perforated screen

4": 1/8" (3mm) 304 stainless steel

perforated screen






Series LF777, LFS777


Wye-Pattern Lead Free* Bronze Strainers

Dimensions – Weights



LF777

SIZE		DIMEN	SIONS		WE	GHT
		A	E	3		
in.	in.	mm	in.	mm	lbs.	kgs
1/4	211/16	68	1 ¹¹ / ₁₆	43	1.7	0.77
3/8	211/16	68	111/16	43	1.7	0.77
1/2	3	76	2	51	1.7	0.77
3/4	35/16	84	25/16	59	1.7	0.77
1	41/2	114	25/16	59	2.7	1.22
11/4	51/8	130	31/8	79	3.0	1.36
1½	57//8	149	3¾	95	4.0	1.81
2	63/16	157	47/8	124	7.4	3.36
21/2	81/8	206	415/16	125	12.0	5.44
3	101//8	257	611/16	170	24.0	10.90
4	13	325	101/2	267	41.0	18 60



LFS777

SIZE		DIMEN		WEIGHT				
		4		В				
in.	in.	mm	in.	mm	lbs.	kgs		
1/2	3%	86	21/16	52	1.5	0.68		
3/4	33/4	95	27/16	63	1.6	0.73		
1	5	127	3	76	2.5	1.13		
11/4	55%	143	31/4	82	2.8	1.25		
1½	67/16	164	313/16	97	4.0	1.81		
2	71/2	191	45%	118	7.4	3.39		


Model 51-1

Dual Limit Switch


Size: 2" - 8" NPT

The Model 51-1 Dual Limit Switch provides visual indication of valve position, as well as remote electrical indication of "valve open" and "valve closed". The single pole double throw Micro-Switches can be connected to open or close an electrical circuit when the valve opens or closes.

The adjustable collars are normally set to contact the trip arms to indicate "valve open" and "valve closed". The collars can be positioned on the stem by loosening the set-screws to actuate the switches at the desired point of valve travel.



Single Pole Double Throw Switch





Specifications

Body Material: Stainless Steel

Elastomers: Buna-N (standard)

EPDM (optional) Viton™ (optional)

Enclosure: NEMA 1, 3, 4 and 13 General Purpose (standard)

NEMA 1,7 and 9 Explosion Proof (optional)

Electrical: Form C SPDT Switch

15 amp. 125, 250 or 480 VAC

½ amp. 125 VDC ¼ amp. 250 VDC ½" Conduit Connection

Viton™ is a trademark of The Chemours Company FC, LLC

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Parts List

ltem	Description							
1	Limit Switch							
2	Bracket							
3	Stem							
4	Trip collar							
5	Set Screw							
6	Сар							
7	Wiper Ring*							
8	0-Ring*							
9	Guide							
10	0-Ring*							
11	Polypak*							
12	Locknut							
13	Body							
14	Pin							
15	Coupling							


*Included in Repair Kit

Installation, Operation and Maintenance - Series LFM513-5 - Large

Installation

- 1. Prior to installation, flush line to remove debris.
- 2. Install valve so the flow arrow matches flow through the line, and gauges to monitor valve inlet and outlet pressures.
- 3. Install isolation valves upstream and downstream of the main valve.
- 4. Provide adequate clearance for valve servicing and maintenance. Refer to valve servicing dimensions on next page. Avoid installing valves 6" and larger in the vertical position (main valve stem horizontal). Automatic Control Valves (ACVs) are designed for horizontal in-line installation, with the cover facing up (main valve stem vertical). Slow operation or premature stem and guide wear may occur if valve is not installed according to factory recommendations. Consult factory for detailed engineering review prior to ordering if valve is to be installed other than horizontally in-line.
- 5. If valve is equipped with a pilot control system, extra precautions should be made during installation to protect the piping circuit from damage. Only remove the pilot control system from the valve if necessary. Tubing and fittings should be kept clean and replaced exactly as removed. Consult appropriate hydraulic schematic to ensure proper re-assembly.
- 6. Connect solenoid wiring leads to desired switching device, using safe, standard electrical practices.
- 7. Wire the limit switch contacts to the proper relay connections, using safe, standard electrical practices. Adjust the limit switch collar to the approximate make/break contact position.

Valve Servicing Dimensions



The following tables detail the recommended minimum valve servicing dimensions.

Globe

Size (in)	2	0	2	24
	in.	cm.	in.	cm.
A (in)	82	209	82	209
B (in)	48	209	82	209

Limited Warranty: Watts Regulator Co. (the "Company") warrants each product to be free from defects in material and workmanship under normal usage for a period of one year from the date of

THE WARRANTY SET FORTH HEREIN IS GIVEN EXPRESSLY AND IS THE ONLY WARRANTY GIVEN BY THE COMPANY WITH RESPECT TO THE PRODUCT. THE COMPANY MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED. THE COMPANY HEREBY SPECIFICALLY DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

The remedy described in the first paragraph of this warranty shall constitute the sole and exclusive remedy for breach of warranty, and the Company shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if this product does not work properly, other costs resulting from labor charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, chemical, or any other circumstances over which the Company has no control. This warranty shall be invalidated by any abuse, misuse, misapplication, improper installation or improper maintenance or alteration of the product.

Some States do not allow limitations on how long an implied warranty lasts, and some States do not allow the exclusion or limitation of incidental or consequential damages. Therefore the above limitations may not apply to you. This Limited Warranty gives you specific legal rights, and you may have other rights that vary from State to State. You should consult applicable state laws to determine your rights. SO FAR AS IS CONSISTENT WITH APPLICABLE STATE LAW, ANY IMPLIED WARRANTIES THAT MAY NOT BE DISCLAIMED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE LIMITED IN DURATION TO ONE YEAR FROM THE DATE OF ORIGINAL SHIPMENT.



USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com Canada: T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca Latin America: T: (52) 55-4122-0138 • Watts.com

© 2022 Watts ES-ACV-LFM513-5-L 2217